



Produktname | *Product name*: Energy Check LCD

Artikelnummer | *Part Number*: 1900-0100


Anfragenummer | *Inquiry Number*: AN14604N

Ersteller / Datum | *Creator / Date*: ka / 2021-05-07

Version	Änderung / Change	Datum / Date	Name
V0	---	2021-10-12	ka

Template name: ANSMANN xxxx-xxxx_0DA, Template version: V50

Zeichnung des Testgerätes / Drawing of the test device:



Allowable deviation / general tolerances DIN ISO 2768-c

Technische Daten des Testgerätes / Technical data of the test device:



Stromversorgung:	Interner 9V E-Block	<i>Power supply:</i>	<i>Internal 9V E-Block</i>
Bedienelemente:	Taster: Test der internen 9V E-Block	<i>Control elements:</i>	<i>Button: Test of the internal 9V E-Block batterie.</i>
LCD Anzeige:	Batteriespannung (in V), Restkapazität (in 10% Schritten)	<i>LCD indicator:</i>	<i>Battery voltage (in V), remaining capacity (in 10% steps)</i>
Gehäusotyp:	Tischgehäuse	<i>Housing type:</i>	<i>Desktop case</i>
Approbationen:	CE	<i>Approvals:</i>	<i>CE</i>
Gewicht:	230 g (Tester ohne 9V Batterie) 275 g (Tester inkl. 1x 9V Batterie)	<i>Weight:</i>	<i>230 g (tester without 9V alkaline battery) 275 g (tester incl. 1x 9V alkaline battery)</i>
Lieferumfang:	- Testgerät - 9V Batterie - Mehrsprachige Bedienungs- anleitung	<i>Shipment:</i>	- <i>Test device</i> - <i>9V battery</i> - <i>Multilingual operating instruction</i>
Verpackung:	Farbige Faltschachtel	<i>Package:</i>	<i>Coloured folding box</i>

Testfunktion für diese Zellen / Test function for these cells:

Knopfzellen / button cells:

1,5V Alkaline:

LR41, LR43, LR44, LR45, LR48, LR50, LR52, LR53, LR54,
LR55, LR57, LR58, LR59, LR60, LR63, LR66, LR69

1,44V Zink-Luft / Zinc-Air:

V10, V13, V675, V312

3V Lithium:

CR1025, CR1216, CR1220, CR1225, CR1616, CR1620, CR1632, CR2016,
CR2025, CR2032, CR2320, CR2330, CR2354, CR2430, CR2450, CR2477, CR3032

Fotobatterien / photo batteries:

3V Lithium:

CR123, CR2

Standard Alkaline Batterien / standard Alkaline batteries:

1,5V Rundzellen / cylindric cells:

AAA, AA, C, D

9V:

9V-E-Block

12V:

A23

Aufladbare Batterien / rechargeable batteries:

1,2V NiCd / NiMH:

AAA, AA, C, D

Li-Ion, Lithium Batterien / Li-Ion, Lithium batteries:

Lithium 1,5V nicht wiederaufladbar / Lithium 1.5V non rechargeable:

AAA, AA

Li-Ion 3,6V/3,7V:

14500, 14650, 16340, 17500, 18500, 18650, 22650, 26650