



Part Number : [2203852011](#)

Product Description : NextStream Connector, 8x, 80 Circuits, 13 HS Channels Max, 1.55mm Shell Leg Length, PCIe Gen 6, with Pick and Place Dust Cap

Series Number : 220385

Status : Active

Product Category : High-Speed I/O Connectors

---

## Documents & Resources

### Drawings

[Drawing 2203852011\\_sd.pdf](#)

[Packaging Design Drawing 2203852011-PK-000.pdf](#)

### 3D Models and Design Files

[3D Model 2203852011\\_stp.zip](#)


### Specifications

[Product Specification 2203850001-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	High-Speed I/O Connectors
Series	220385
Description	NextStream Connector, 8x, 80 Circuits, 13 HS Channels Max, 1.55mm Shell Leg Length, PCIe Gen 6, with Pick and Place Dust Cap
Application	Wire-to-Board
Component Type	Receptacle
Product Family	NextStream Connector System
Product Name	NextStream
Type	Internal
UPC	196823268540

### Electrical

Current - Maximum per Contact	1.1A
Data Rate	64 Gbps (PAM-4)
Voltage - Maximum	30V AC (RMS)/DC

### Physical

Circuits (Loaded)	80
Circuits (maximum)	80
Color - Resin	Black
Durability (mating cycles max)	200
Gender	Receptacle
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Performance Thermoplastic

Number of Pairs	13
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	0.60mm
Pitch - Termination Interface	0.60mm
Plating min - Mating	0.762µm
Plating min - Termination	0.025µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
NextStream Straight-to-NextStream Straight Cable Assemblies	<u>220750</u>
NextStream Right-Angle-to-NextStream Right-Angle Cable Assemblies	<u>220751</u>
NextStream Side-Exit-to-NextStream Side-Exit Cable Assemblies	<u>224863</u>