


COAXIAL CONNECTOR, SK, 50 Ohm, Edge mount PCB jack (female)

92_SK-S50-0-200/199_N

Properties

- For microstrip configurations
- Fast and easy installation
- Precision testing up to 40 GHz
- Reusable design
- Mechanical intermateable with SMA and PC 3.5 (3.5 mm standard)

**Product configuration**

Interface type	Gender	Standard
SK	jack	MIL-STD-348B

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Stainless Steel	Passivated (Plating)
Insulator	PEI (Polyether-imide)	

Electrical data

Impedance	50 Ω
Interface frequency	40 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 40 GHz	17 dB	1.33

Mechanical data

Weight	0.0043 kg
Mating cycles	500

Environmental data

Operation temperature	-40 °C ... 165 °C
-----------------------	-------------------

COAXIAL CONNECTOR, SK, 50 Ohm, Edge mount PCB jack (female)

92_SK-S50-0-200/199_N

Ordering Information Table	
Item number	Item description
85221630	92_SK-S50-0-200/199_NE

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P41030 / Date of publication: 23.05.2024 / uncontrolled copy