multicomp PRO

Palm Size Digital Multimeters



Description

The new generation Palm Size Multimeters redefines the performance standards for entry-level digital multimeters. These models ensures that users can work safely in CAT II 250V environment.

Features

Clear LCD Display
Equipped with Comfortable Protective Cover, Test Probe Holder
2 Meters Drop Test, Precision Protection
Auto Power Off
Auto Backlight Off
Loud Buzzer Sound
Knobs Shift Smoothly, In-line with Ergonomics

Specification Table

Characteristics	72-13430	72-13435	72-13440	
Max Display	1999			
Range Selection	Auto Manual			
Diode Test	✓			
Continuity Buzzer	✓			
Overload Alarm	✓			
Data Hold	✓			
Relative Mode	✓		-	
Low Battery Indication	√			
NCV	-	-	√	
DC Voltage	200mV/2V/20V/200V/250V, ±(0.8%+1)	200mV/2000mV/20V/200V/250V, ±(0.5%+2)	200mV/2000mV/20V/200V/250V, ±(0.5%+2)	
AC Voltage	200mV/2V/20V/200V/250V, ±(1% +2)	200V/250V, ± (1.2%+3)	200V/250V, ±(1.2%+10)	
AC Current	200μA/2000μA/20mA/ 200mA/2A/10A, ±(1.2%+3)	-	-	
DC Current	200μA/2000μA/20mA/ 200mA/2A/10A, ±(1%+3)	2000μA/20mA/ 200mA/10A, ±(1%+3)	2000μA/20mA/ 200mA/10A, ±(1%+3)	
Capacitance	2nF/20nF/200nF/2uF/ 20uF/200uF, ±(3%+5)	-	-	

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk

Page <1> 09/03/18 V1.0

Palm Size Digital Multimeter



Characteristics	72-13430	72-13435	72-13440	
Resistance	$200\Omega/2$ kΩ/ 20 kΩ/ 200 kΩ/ 2 MΩ/ 20 MΩ/ 20 0MΩ, $\pm (0.8\%+2)$	200Ω/2kΩ/20kΩ/200kΩ/20MΩ, \pm (0.8%+2)	$\begin{array}{c} 200\Omega/2k\Omega/20k\Omega/200k\Omega/\\ 2M\Omega/20M\Omega/200M\Omega,\\ \pm(0.8\%+2) \end{array}$	
Temperature	-	-40°C to 1000°C	-	
	-	-40°F to 1832°F	-	
Power	AAA 1.5V × 2			
Standard Accessories	Type K Thermocouple (Part Number 72-13435 only), English Manual, Test Leads, Protective Case			
Product Weight	206g (Battery Included)			
Product Size	134mm × 77mm × 47mm			

Part Number Table

Description	Part Number
DMM, Handheld, Auto/Manual, 2000 Count	72-13430
DMM, Handheld, Manual, 2000 Count	72-13435
DMM, Handheld, Manual, 2000 Count	72-13440

Important Notice: This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk

