

Johanson Product Information for VPDF202W222K1GV001E

**Johanson Company: Johanson Dielectrics inc.**

Product Release Date: 03 January, 2006

Deprecated P/N: 202S41W222KV4E

Web Page Link:

<https://www.johansondielectrics.com/high-voltage-mlc-capacitors>

Datasheet Date: 04-15-2024

Description: Capacitors HVS PME, 1210, X7R, 2000V, 2200pF±10%, Ni/Sn (RoHS), 7" Reel Embossed Tape

Size for Capacitors (EIA): 1210

Thickness (Max): 0.080

Life Cycle Stage: Active - Production

End Band (Min):

Schedule B: 8532

End Band (Max):

ECCN: EAR99

Standard Item: 1

RoHS Compliance: Yes, RoHS 10/10

Lead Time Typical (Weeks)\*:

\*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes. 10

REACH: 1

Country of Origin: CN

Length (Min): 0.115

Product Family: Capacitors

Length (Max): 0.135

Product Subfamily: Capacitors High Voltage PME SMD ? 500V

Width (Min): 0.085

Capacitance Value: 2200.000

Width (Max): 0.105

Cap Unit of Meas: pF

Packaged Weight (lb) Arm: 0.45

Tolerance: ±10%

Packaging: 7" Reel Embossed Tape

Voltage: 2000.0

Operating Temp Range: -55°C to +125°C

Dielectric Temp Coefficient: X7R

Storage Temp Range (Packaged): -65°C to +125°C

Termination: 68

Storage Temp Range (Non Operating): +5°C to +40°C with RH 20% to 70%

Marking: No Mark