

Johanson Product Information for VPDP502G330J1GV001E

Johanson Company: Johanson Dielectrics inc.

Product Release Date: 09 January, 2006

Deprecated P/N: 502R29N330JV4E

Web Page Link:

<https://www.johansondielectrics.com/high-voltage-mlc-capacitors>

Datasheet Date: 04-15-2024

Description: Capacitors HVS PME, 1808, NP0/C0G, 5000V, 33pF±5%, Ni/Sn (RoHS), 7" Reel Embossed Tape

Size for Capacitors (EIA): 1808

Thickness (Max): 0.085

Life Cycle Stage: Active - Production

End Band (Min):

Schedule B: 8532

End Band (Max):

ECCN: EAR99

Standard Item: 1

RoHS Compliance: Yes, RoHS 10/10

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes. 10

REACH: 1

Product Family: Capacitors

Length (Min): 0.165

Product Subfamily: Capacitors High Voltage PME SMD ? 500V

Length (Max): 0.205

Capacitance Value: 33.000

Width (Min): 0.070

Cap Unit of Meas: pF

Width (Max): 0.090

Tolerance: ±5%

Packaging: 7" Reel Embossed Tape

Voltage: 5000.0

Packaging Qty: 2000

Dielectric Temp Coefficient: NP0/C0G

Operating Temp Range: -55°C to +125°C

Termination: 68

Storage Temp Range (Packaged): -65°C to +125°C

Marking: No Mark

Storage Temp Range (Non Operating): +5°C to +40°C with RH 20% to 70%