


MCCOG21605D6W-FPTLWI	2 x 16	5mm Character Height	LCD Module
<b>Specification</b>			
Version: 1		Date: 23/04/2024	
<b>Revision</b>			
1	17/10/2016	First Issue	
2	22/04/2024	Updated Drawing	

Display Features			
Character Count	2 x 16		
Appearance	Black on White		
Logic Voltage	5V		
Interface	I2C		
Font Set	English / Japanese		
Display Mode	Transflective		
Character Height	4.67mm		
LC Type	FSTN		
Module Size	62.80 x 23.00 x 6.30 mm		
Operating Temperature	-20°C ~ +70°C		
Construction	COG		
LED Backlight	White		
		---	---

\* - For full design functionality, please use this specification in conjunction with the ST70321 specification. (Provided Separately)



Display Accessories	
Part Number	Description
MCCOG-I2C-I-8	Fine pitch(1.27mm) COG I2C interface board. Compatible with both Arduino and UC32 controller boards.

Optional Variants		
Fonts	Appearances	Voltage
	Black on Yellow/Green White on blue	



## Mechanical Specifications

Module Size	62.80 x 23.00 x 6.30 ( With Backlight)				W x H x D mm
Viewing Area	51.50 x 12.20	W x H mm	Hole-to-Hole	---	W x H mm
Character Size	2.60 x 4.67	W x H mm	Character Pitch	3.00 x 5.07	W x H mm
Dot Size	0.48 x 0.54	W x H mm	Dot Pitch	0.53 x 0.59	W x H mm



## Pin Layout

PI	SYMBOL	DESCRIPTION	REMARKS
1	VOUT	DC/DC Voltage Converter	
2	CAP1N	Voltage booster Circuit (VDD-VSS)	
3	CAP1P		
4	VDD	Power Supply	5.0V
5	VSS	Ground	
6	SDA	Input Data	
7	SCL	Clock Input Data	
8	RST	Reset	

MIDAS  
DISPLAYS

---

DESIGN • MANUFACTURE • SUPPLY



# Font Map

Upper 4bit Lower 4bit	LLLL	LLLH	LLHL	LLHH	LHLL	LHLH	LHHL	LHHH	HLLL	HLLH	HLHL	HLHH	HHLL	HHLH	HHHL	HHHH
LLLL	CG RAM (1)															
LLLH	(2)															
LLHL	(3)															
LLHH	(4)															
LHLL	(5)															
LHLH	(6)															
LHHL	(7)															
LHHH	(8)															
HLLL	(1)															
HLLH	(2)															
HLHL	(3)															
HLHH	(4)															
HHLL	(5)															
HHLH	(6)															
HHHL	(7)															
HHHH	(8)															



Absolute Maximums Ratings					
Item	Symbol	Minimum	Typical	Maximum	Unit
Power Supply (Logic)	V <sub>DD</sub>	-0.3	---	6.0	V
Power Supply (LCD)	V <sub>0</sub>	7.0	---	-0.3	V
Operating Temperature	T <sub>OP</sub>	-20°C	---	70°C	°C
Storage temperature	T <sub>ST</sub>	-30°C	---	80°C	°C

Electronic Characteristics						
Item	Symbol	Condition	Minimum	Typical	Maximum	Unit
Input Voltage High	V <sub>IH</sub>	---	0.70	---	V <sub>DD</sub>	V
Input Voltage Low	V <sub>IL</sub>	---	---	---	0.20	V
Output Voltage High	V <sub>OH</sub>	---	0.80	---	V <sub>DD</sub>	V
Output Voltage Low	V <sub>OL</sub>	---	---	---	0.20	V
Supply Voltage Logic	V <sub>DD</sub> ~ V <sub>SS</sub>	---	3.00	3.30	5.00	V
Supply Voltage LCD	V <sub>DD</sub> ~ V <sub>0</sub>	T <sub>a</sub> =25°C	---	4.50	---	V
Supply Current	I <sub>DD</sub>	---	---	0.18	---	mA

LCD Characteristics						
For STN/FSTN LCD Panel Types						
Item	Symbol	Condition	Minimum	Typical	Maximum	Unit
Viewing Angle	Φ <sub>2</sub> - Φ <sub>1</sub>	CR ≥ 2	30	---	60	ψ=180°
	Θ					
Contrast Ratio	CR	---	---	5	---	---
Response Time (Rise)	T <sub>R</sub>	---	---	250	400	ms
Response Time (Fall)	T <sub>F</sub>	---	---	100	250	ms

LED Characteristics						
Item	Symbol	Condition	Minimum	Typical	Maximum	Unit
Supply Current	I <sub>LED</sub>	V=3.5V	28.8	32	50	mA
Supply Voltage	V	---	3.40	3.50	3.60	V
Reverse Voltage	V <sub>R</sub>	---	---	---	5	V
Luminance (Without LCD)	I <sub>V</sub>	I <sub>LED</sub> =32mA	441.60	552	---	Cd/m <sup>2</sup>
---	---	---	---	---	---	---
LED Life Time	---	I <sub>LED</sub> =32mA	---	50K	---	Hour

**Attention:** It is constant current, not constant voltage, which should be applied when driving the LED backlight, please ensure you adhere to this rule.

