

RoHS
Compliant



T23A050ASR2-15



T23B050ASR2-15

Specifications


Electrical Rating	: 15A, 125V AC (Resistive Load) 10A, 250V AC (Resistive Load) 16A, 250V AC (Resistive Load)
Operation Temperature	: +50°C to +175°C
*Temperature Tolerance	: ±3K and ±5K
Differential	: 10K to 30K (15K Standard)
Heat Durability	: 220°C Max. (PPS)
Circuit Resistance	: 50mΩ Max.
Insulation Resistance	: 100MΩ Min. at DC500V
Dielectric Strength	: 1,000V AC for one minutes or 1800V AC for one Second.
Operating Life	: 100000 Cycles (15A, 125V/10A 250V AC) 10000 Cycles (16A 250V AC)
Weight	: 4.6g Max.

*Temperature Tolerance		
Grade	Part Number	
	T23A050ASR2-15	T23B050ASR2-15
Action ±°C	50°C ±3°C	60°C ±5°C
Reset ±°C	35°C ±4°C	45°C ±8°C


Contact Type

Part Number	Conditions	Diagram
T23A050ASR2-15	Contact Opens when temperature rises to set point (Normally Closed)	
T23B050ASR2-15	Contact Closes when temperature raises to set point (Normally Open)	

Bracket Type Loose Bracket




Terminal Orientation



R TYPE
(90°)

Terminal Size



TYPE 2
Amp #250 TAB

Part Number Table

Description	Part Number
Thermostat Switch, 50°C, Normally Closed, Flange Mount	T23A050ASR2-15
Thermostat Switch, 50°C, Normally Open, Flange Mount	T23B050ASR2-15

Dimensions : Millimetres (Inches)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro