



Wire Protection & Management > Adhesives & Sealants > Epoxy Adhesives



Packaging Method: **Dual Pack**

Packaging Quantity: 1

Heat Resistance Temperature (Max): 150 °C

Features

Body Features

Color (Supplied)	Black, Gray
Material Systems Code	25

Usage Conditions

Heat Resistance Temperature (Max)	150 °C
-----------------------------------	--------

Packaging Features

Packaging Method	Dual Pack
Packaging Quantity	1

Other

Curing Method	20 °C for 24 hr, 85 °C for 1 hr
Pot Life	90 minute

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC















Halogen Content Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free









Solder Process Capability Not applicable for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # CAT-R21-731072 Bulbous Heat Shrink Boots: Lipped, Straight</p>	 <p>TE Part # CAT-R21-7310654 Heat Shrink Boots: Non Lipped, Right Angle</p>	 <p>TE Part # CAT-R21-731 Heat Shrink Boots: Non Lipped, Straight</p>	 <p>TE Part # CAT-R21-73106549 Bulbous Heat Shrink Boots: Lipped, Right Angle</p>
 <p>TE Part # CAT-R21-7310554 Heat Shrink Boots: Lipped, Right Angle</p>	 <p>TE Part # CAT-R21-7310723 Low Profile Heat Shrink Boots: Poly Molded, Lipped, Straight</p>	 <p>TE Part # CAT-R21-731055 Low Profile Heat Shrink Boots: Poly Mold, Lipped, Right Angle</p>	 <p>TE Part # CAT-R21-73107237 Heat Shrink Boots: Lipped, Straight</p>
 <p>TE Part # CAT-R21-73105 Heat Shrink Boots: Micro Molded, Lipped, Right Angle</p>	 <p>TE Part # CAT-R21-731055422 Heat Shrink Boots: Poly Mold, Lipped</p>	 <p>TE Part # 820243-000 462A034-25-0</p>	 <p>TE Part # 820120-000 382A046-25-0</p>



Customers Also Bought



Documents



Product Drawings

S1125-KIT-8

English

Datasheets & Catalog Pages

Adhesives Selection Guide

English

Solutions for Defense Applications Certified to VG Standards

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English