

COAXIAL CONNECTOR, TNC, 50 Ohm, Straight bulkhead cable jack (female)

24_TNC-50-4-79/199_N

Properties

- Excellent corrosion resistance in a wide range of environments
- High salt mist resistant
- Material 316L stainless steel
- Excellent return loss values
- Applicable in frequencies up to 11 GHz



Product configuration

Interface type	Gender	Standard
TNC	jack	IEC 60169-17_MIL-STD-348A/313_CECC 22200

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Stainless Steel (high salt mist resistant)	Passivated (Plating)
Body	Stainless Steel (high salt mist resistant)	Passivated (Plating)
Insulator	PTFE (Polytetrafluoroethylene)	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Stainless Steel (high salt mist resistant)	Passivated (Plating)
Washer	Bronze	Nickel Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data

Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 2 GHz	32 dB	1.05
2 GHz ... 4 GHz	23 dB	1.15
4 GHz ... 8 GHz	21 dB	1.20

COAXIAL CONNECTOR, TNC, 50 Ohm, Straight bulkhead cable jack (female)

24_TNC-50-4-79/199_N

Mechanical data	
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

Environmental data	
Operation temperature	-65 °C ... 165 °C
Ingress protection (IP Rating)	Mated / IP67

Ordering Information Table		
Item number	Item description	Packaging type
85180287	24_TNC-50-4-79/199_NE	Single

Suitable cables	
Cable group	X34 - 4 mm / 50 Ohm X28 - 4 mm / 50 Ohm
Suitable cables	Spuma_240-RS-FR SPUMA_195-FR-01

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P43698 / Date of publication: 07.03.2024 / uncontrolled copy