

DOS-0803-WSK

Field-attachable connectors

PLUG CONNECTORS AND CABLES



Illustration may differ

Ordering information

| Туре | Part no. |
|--------------|----------|
| DOS-0803-WSK | 6053168 |

Please consider the operational voltage of the connector. For sensors with an integrated cable and flying leads the operational voltage of the connector can be lower than the operational voltage of the sensor.

Other models and accessories

www.sick.com/Field-attachable_connectors



Detailed technical data

Technical specifications


| Accessory group Plug connectors and cables Accessory family Field-attachable connectors Connection type head A Female connector, M8, 3-pin, angled Connector type Screw-type terminals Connector material PBT Connector color Black Locking nut material Nickel-plated brass Tightening torque 0.6 Nm Shielding Unshielded Permitted cross-section 0.14 mm² 0.5 mm² Reference voltage ≤ 60 V Current loading 4 A UL File No. E335179 Enclosure rating IP67 Ambient operating temperature -40 °C +85 °C | | |
|--|-------------------------------|--|
| Connection type head A Connector type Screw-type terminals Connector material PBT Connector color Black Locking nut material Nickel-plated brass Tightening torque O.6 Nm Shielding Unshielded Permitted cross-section Reference voltage ≤ 60 V Current loading UL File No. E335179 Enclosure rating Ambient operating temperature | Accessory group | Plug connectors and cables |
| Connection type Screw-type terminals Connector material PBT Connector color Black Locking nut material Nickel-plated brass Tightening torque 0.6 Nm Shielding Unshielded Permitted cross-section 0.14 mm² 0.5 mm² Reference voltage ≤ 60 V Current loading 4 A UL File No. E335179 Enclosure rating IP67 Ambient operating temperature | Accessory family | Field-attachable connectors |
| Connector material PBT Connector color Black Locking nut material Nickel-plated brass Tightening torque 0.6 Nm Shielding Unshielded Permitted cross-section 0.14 mm² 0.5 mm² Reference voltage ≤ 60 V Current loading 4 A UL File No. E335179 Enclosure rating IP67 Ambient operating temperature | Connection type head A | Female connector, M8, 3-pin, angled |
| Connector color Locking nut material Nickel-plated brass Tightening torque 0.6 Nm Shielding Permitted cross-section Reference voltage ≤ 60 V Current loading UL File No. E335179 Enclosure rating Ambient operating temperature | Connection type | Screw-type terminals |
| Locking nut material Nickel-plated brass Tightening torque 0.6 Nm Shielding Unshielded Permitted cross-section 0.14 mm² 0.5 mm² Reference voltage ≤ 60 V Current loading 4 A UL File No. E335179 Enclosure rating IP67 Ambient operating temperature | Connector material | PBT |
| Tightening torque Shielding Permitted cross-section Reference voltage ≤ 60 V Current loading UL File No. Enclosure rating Ambient operating temperature 0.6 Nm Unshielded 0.14 mm² 0.5 mm² 0.4 Mm² 0.5 mm² 4 A UL File No. E335179 IP67 | Connector color | Black |
| Shielding Permitted cross-section Reference voltage ≤ 60 V Current loading UL File No. Enclosure rating Ambient operating temperature Unshielded 0.14 mm² 0.5 mm² 4 A Enclosure rating IP67 | Locking nut material | Nickel-plated brass |
| Permitted cross-section Reference voltage ≤ 60 V Current loading UL File No. Enclosure rating Ambient operating temperature 0.14 mm² 0.5 mm² 4 A Enclosure rating IP67 | Tightening torque | 0.6 Nm |
| Reference voltage ≤ 60 V Current loading 4 A UL File No. E335179 Enclosure rating IP67 Ambient operating temperature | Shielding | Unshielded |
| ≤ 60 V Current loading UL File No. Enclosure rating Ambient operating temperature | Permitted cross-section | 0.14 mm ² 0.5 mm ² |
| Current loading 4 A UL File No. E335179 Enclosure rating IP67 Ambient operating temperature | Reference voltage | |
| UL File No. E335179 Enclosure rating IP67 Ambient operating temperature | | ≤ 60 V |
| Enclosure rating IP67 Ambient operating temperature | Current loading | 4 A |
| Ambient operating temperature | UL File No. | E335179 |
| | Enclosure rating | IP67 |
| Head -40 °C +85 °C | Ambient operating temperature | |
| | Head | -40 °C +85 °C |

Classifications

| ECLASS 5.0 | 27279290 |
|--------------|----------|
| ECLASS 5.1.4 | 27279290 |
| ECLASS 6.0 | 27279221 |
| ECLASS 6.2 | 27279221 |
| ECLASS 7.0 | 27440104 |
| ECLASS 8.0 | 27440104 |
| ECLASS 8.1 | 27440104 |
| ECLASS 9.0 | 27440102 |
| ECLASS 10.0 | 27440102 |
| ECLASS 11.0 | 27440102 |

| ECLASS 12.0 | 27440116 |
|----------------|----------|
| ETIM 5.0 | EC002635 |
| ETIM 6.0 | EC002635 |
| ETIM 7.0 | EC002635 |
| ETIM 8.0 | EC002635 |
| UNSPSC 16.0901 | 39121421 |

Dimensional drawing (Dimensions in mm (inch))



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

