

2474603-2 ✓ ACTIVE

TE Internal #: 2474603-2

Applicators, Pneumatic Feed, OCEAN, Male Adapter Post - Atlantic Style Interface, TE Stripper / Crimper, Wire Crimp Width .037 in [.94 mm], F-Crimp

[View on TE.com >](#)



Application Tooling > Applicators



Applicator Feed Type: **Pneumatic**

Applicator & Product Style: **OCEAN**

Application Interface: **Male Adapter Post - Atlantic Style**

Terminator Type: **TE Stripper / Crimper**

Wire Crimp Width: **.94 mm [.037 in]**

Features

Contact Features

Crimp Type	F-Crimp
------------	---------

Dimensions

Wire Stripping Length	2.4 mm[.094 in]
Wire Crimp Width	.94 mm[.037 in]

Other

Applicator Feed Type	Pneumatic
Applicator & Product Style	OCEAN
Application Interface	Male Adapter Post - Atlantic Style
Terminator Type	TE Stripper / Crimper
Service Options	Crimped Samples
Alignment Aids	Alignment Gauge

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2024
(240)
Not Yet Reviewed

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 2468544-1
Ethernet SC Mach ESM-10, with AI vision



TE Part # 2468544-2
Ethernet SC Mach ESM-10

Documents

Datasheets & Catalog Pages

[TE_APPLICATORS_CATALOG](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English