


Data Sheet PUM-3546L-R

Specifications

Parameters	Values	Units
Sensitivity (0 dB=1V/Pa @ 1kHz)	-46 ± 4	dB
Rated Voltage	2.0	VDC
Operating Voltage Range	2.0 ~ 10	VDC
Current consumption max	0.5	mA
Signal-to-Noise Ratio	>55	dB
Frequency Range	$100 \sim 10,000$	Hz
Maximum SPL Input (THD<3%) Acoustic Overload Point	110	dB
Directivity	Uni-Directional	-
Environmental Compliances	RoHS/REACH	-
Operating Temperature	-20 ~ 60	°C
Storage Temperature	-40 ~ 70	°C


Typical Frequency Response



This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited.

©2021, PUI Audio Inc.

Recommended Drive Circuit



Microphone Handling Precautions


High temperature and/or static electricity may damage microphones. To ensure careful handling, we suggest following these precautions:


- Ensure the power rating of the soldering iron is below 90 watts
- The temperature of the soldering iron must be limited to 360°C ±10°C (680°F ±50°F)
- Soldering duration for each terminal shall be at or under 2 seconds
- If practical, use a metal fixture to hold the microphone in-place and to act as a heatsink. A fixture should have appropriate diameter holes drilled through the entire fixture to prevent pressure from being placed on the diaphragm (as below)




©2021, PUI Audio Inc.

Dimensions







Specifications Revisions

Revision	Description	Date
-	Released from Engineering	1/31/2006
A	Added Terminal Polarity	2/5/2007
В	Revised to Inventor 3D Image	10/25/2010
С	Update Drawing Image, Sensitivity Toleranace	8/3/2022

Note:

- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are ± 0.5 mm and angles are $\pm 3^{\circ}$.
- 2. Specifications subject to change or withdrawal without notice.