


Data Sheet SMT-0827-TW-3V-R

Specifications


Parameters	Values	Units	
Rated Voltage	3.6	V0-p	
Operating Voltage Range	2 ~ 5	V0-p	
Current Draw at Rated Voltage	70	mA	
Coil Resistance	15 ± 3	Ohms	
Minimum SPL @ 10cm	85	dBA	
Resonant Frequency	2730 ± 500	Hz	
Housing Material	LCP	-	
Terminal Material	Sn Plated Brass	-	
Weight	2	Grams	
Acceptable Soldering Methods	Manual/Reflow	See Details	
Environmental Compliances	RoHS/REACH	-	
Storage Temperature	-50 ∼ + 95	°C	
Operating Temperature	-40 ∼ +85	°C	

$Measurement\ Method\ {\it (Temperature: 25\pm3°C; Relative\ Humidity: 60\% \sim 70\%)}$

Standard Test Fixture (Distance: 10cm, 5 V0-p, 2400 Hz square wave)



Typical Frequency Response (3.6V, 10cm)




Reliability Testing

Type of Test	Test Specifications
High Temperature Test	96 hours at 95°C without applying power. Expose for 2 hours at room temp.
Low Temperature Test	96 hours at -50°C without applying power.
Humidity Test	96 hours at 40°C with relative humidity at 90-95% without applying power. Expose for 2 hours at room temp.
	Test 5 cycles as shown below.
Temperature Cycle Testing	+95°C +20°C +20°C +20°C 30min 15min 30min 15min
	9.3g Amplitude:1.5mm Time:1min/axis
Vibration Test	Apply in each X,Y,Z direction for 2 hours each.
Drop Test	Free drop from 100cm height to 10mm thick board in X,Y,Z direction.


After tests, part shall measure within ±5dB.

Suggested Reflow




^{*}Manual soldering with 350C iron temp and 2-3 seconds solder time per terminal.

Dimensions




©2021, PUI Audio Inc.

Packaging



1ROLL CARRIER REEL/INNER BOX;1卷套防静电袋抽真空放入一内盒



3000PCS/CTN 每箱放3000只(5只内盒)

Specifications Revisions

Revision	Description	Date
-	RELEASED FROM ENGINEERING	03/29/2007
A	Revised to Inventor 3D Template	11/5/2007

Note:

- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are ± 0.5 mm and angles are $\pm 3^{\circ}$.
- 2. Specifications subject to change or withdrawal without notice.