





## FEATURES

- \* Current transfer ratio  
( CTR : MIN. 50% at  $I_F = 5\text{mA}$ ,  $V_{CE} = 5\text{V}$  )
  
- \* Isolation voltage between input and output  
(  $V_{iso} = 3\text{KVrms}$  )
  
- \* Compact dual-in-line package  
4 channels type
  
- \* Employs double transfer mold technology
  
  
- \* ROHS compliance
- \* G : Halogen Free


## APPLICATIONS

- \* Hybrid substrates that require high density mounting.
- \* Programmable controllers
- \* System appliances, measuring instruments

## OUTLINE DIMENSIONS




PIN NO. AND INTERNAL CONNECTION DIAGRAM




1,3,5,7. Anode  
 2,4,6,8. Cathode

9,11,13,15. Emitter  
 10,12,14,16. Collector



- \*1. 3-digit date code.
- \*2. Rank shall be or shall not be marked.

## TAPING DIMENSIONS



Description	Symbol	Dimension in mm (inches)
Tape wide	W	16 ± 0.3 (.47)
Pitch of sprocket holes	P <sub>0</sub>	4 ± 0.1 (.15)
Distance of compartment	F	7.5 ± 0.1 (.217)
Distance of compartment to compartment	P <sub>1</sub>	2 ± 0.1 (.079)

### Quantities per Reel :

Package Type	
Quantities (pcs)	<b>2000</b>

## ABSOLUTE MAXIMUM RATING

( Ta = 25°C )

PARAMETER		SYMBOL	RATING			UNIT
			217	227	247	
INPUT	Forward Current	I <sub>F</sub>	50			mA
	Reverse Voltage	V <sub>R</sub>	6			V
	Power Dissipation	P	70			mW
OUTPUT	Collector - Emitter Voltage	V <sub>CEO</sub>	80			V
	Emitter - Collector Voltage	V <sub>ECO</sub>	7			V
	Collector Current	I <sub>C</sub>	50			mA
	Collector Power Dissipation	P <sub>C</sub>	150	100		mW
Total Power Dissipation		P <sub>tot</sub>	200	170		mW
*1	Isolation Voltage	V <sub>iso</sub>	3,750			V <sub>rms</sub>
Operating Temperature		T <sub>opr</sub>	-55 ~ +110			°C
Storage Temperature		T <sub>stg</sub>	-55 ~ +150			°C
*2	Soldering Temperature	T <sub>sol</sub>	260 (10s)			°C

\*1. AC For 1 Minute, R.H. = 40 ~ 60%

Isolation voltage shall be measured using the following method.

- (1) Short between anode and cathode on the primary side and between collector and emitter on the secondary side.
- (2) The isolation voltage tester with zero-cross circuit shall be used.
- (3) The waveform of applied voltage shall be a sine wave.

\*2. For 10 Seconds

## ELECTRICAL - OPTICAL CHARACTERISTICS


( Ta = 25°C )

PARAMETER		SYMBOL	MIN.	TYP.	MAX.	UNIT	CONDITIONS
INPUT	Forward Voltage	V <sub>F</sub>	—	1.2	1.4	V	I <sub>F</sub> =20mA
	Reverse Current	I <sub>R</sub>	—	—	10	μA	V <sub>R</sub> =4V
	Terminal Capacitance	C <sub>t</sub>	—	30	250	pF	V=0, f=1KHz
OUTPUT	Collector Dark Current	I <sub>CEO</sub>	—	—	100	nA	V <sub>CE</sub> =50V, I <sub>F</sub> =0
	Collector-Emitter Breakdown Voltage	BV <sub>CEO</sub>	80	—	—	V	I <sub>C</sub> =0.1mA I <sub>F</sub> =0
	Emitter-Collector Breakdown Voltage	BV <sub>ECO</sub>	7	—	—	V	I <sub>E</sub> =10μA I <sub>F</sub> =0
TRANSFER CHARACTERISTICS	Collector Current	I <sub>C</sub>	2.5	—	30	mA	I <sub>F</sub> =5mA V <sub>CE</sub> =5V
	*1 Current Transfer Ratio	CTR	50	—	600	%	
	Collector-Emitter Saturation Voltage	V <sub>CE(sat)</sub>	—	—	0.4	V	I <sub>F</sub> =2.4mA I <sub>C</sub> =8mA
	Isolation Resistance	R <sub>iso</sub>	5×10 <sup>10</sup>	1×10 <sup>11</sup>	—	Ω	DC500V 40 ~ 60% R.H.
	Floating Capacitance	C <sub>f</sub>	—	0.6	1	pF	V=0, f=1MHz
	Response Time (Rise)	t <sub>r</sub>	—	3	18	μs	V <sub>CE</sub> =2V, I <sub>C</sub> =2mA R <sub>L</sub> =100Ω
	Response Time (Fall)	t <sub>f</sub>	—	4	18	μs	


$$*1 \text{ CTR} = \frac{I_C}{I_F} \times 100\%$$

## CHARACTERISTICS CURVES


**Figure 1. Collector Power Dissipation vs. Ambient Temperature**




**Figure 2. Forward Current vs. Ambient Temperature**




**Figure 3. Forward Current vs. Forward Voltage**




**Figure 4. Forward Voltage Temperature Coefficient vs. Forward Current**



**Figure 5. Pulse Forward Current vs. Duty Cycle Ratio**




**Figure 6. Pulse Forward Current vs. Pulse Forward Voltage**




## CHARACTERISTICS CURVES


**Figure 7. Collector-Emitt Saturation Voltage vs. Forward Current**




**Figure 8. Collector Current vs. Collector-Emitt Voltage**




**Figure 9. Collector Current vs. Small Collector-Emitt Voltage**




**Figure 10. Collector Current vs. Forward Current**



**Figure 11. Collector Dark Current vs. Ambient Temperature**




**Figure 12. Current Transfer Ratio vs. Forward Current**



## CHARACTERISTICS CURVES



**Figure 13. Collector-Emitter Saturation Voltage vs. Ambient Temperature**

**Figure 14. Collector Current vs. Ambient Temperature**




**Figure 15. Switching Time vs. Load Resistance**

**Figure 16. Switching Time vs. Ambient Temperature**





**Figure 17. Frequency Response**





## SWITCHING TIME TEST CIRCUIT




## TEMPERATURE PROFILE OF SOLDERING REFLOW

(1) One time soldering reflow is recommended within the condition of temperature and time profile shown below.

1. Wave solder  
- 260 °C / 10 sec

2. IR reflow

Profile item	Condition
<b>Preheat</b>	
- Temperature Min ( $T_{smin}$ )	150 °C
- Temperature Max ( $T_{smax}$ )	180 °C
- Time (min to max) ( $t_s$ )	90 ± 30 sec
<b>Soldering zone</b>	
- Temperature ( $T_L$ )	250 °C
- Time ( $t_L$ )	10 ~15 sec
<b>Peak temperature (<math>T_p</math>)</b>	260 °C
<b>Ramp-down rate</b>	3 ~ 6 °C / sec



## TEMPERATURE PROFILE OF SOLDERING REFLOW

(2) When using another soldering method such as infrared ray lamp, the temperature may rise partially in the mold of the device.

Keep the temperature on the package of the device within the condition of above (1)

### Notes:

- Isocom is continually improving the quality, reliability, function or design and Isocom reserves the right to make changes without further notices.
- The products shown in this publication are designed for the general use in electronic applications such as office automation equipment, communications devices, audio/visual equipment, electrical application and instrumentation.
- For equipment/devices where high reliability or safety is required, such as space applications, nuclear power control equipment, medical equipment, etc, please contact our sales representatives.
- When requiring a device for any "specific" application, please contact our sales in advice.
- If there are any questions about the contents of this publication, please contact us at your convenience.
- The contents described herein are subject to change without prior notice.
- Do not immerse unit's body in solder paste.