

Actuator

46-
290J.1000.7PD

Distribution by
Newark



<https://newark.eao.com/p/46-290J.1000.7PD>

Your product:



46-290J.1000.7PD Actuator

FRONT

Front bezel colour:	Black
Front dimension:	Ø 29 mm
Front form:	round
Front bezel material:	Plastic

MOUNTING

Design:	raised
Mounting cut-out:	Ø 22.3 mm

ELECTRICAL CHARACTERISTICS

Protection class:	II
--------------------------	----

MECHANICAL CHARACTERISTIC

Switching action:	Maintained (a) - Maintained
Switching angle:	120°
Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)
Switching positions:	2 positions
Weight:	0.08 kg
Mechanical lifetime:	50 000 cycles of operation

AMBIENT CONDITION

Shock resistance:	30g, 18ms (EN-IEC 60068-2-27) 50g, 11ms (EN-IEC 60068-2-27)
--------------------------	--


IP front protection: IP65
Climate resistance: +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)
IK front protection: IK06
Operating temperature: - 25 °C ... + 55 °C
Vibration resistance: 5g f= 2...500Hz (EN-IEC 60068-2-6)

CERTIFICATE


Standards: CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508
Conformities: CE
Approbations: CSA, EAC, UL

OTHER

Short Description: Actuator, Ø 22.3 mm, Ø 29 mm, round, Black, Plastic, Maintained (a) - Maintained, IP65, IK06
Housing colour: Black
max. number of switching elements: 8
Housing material: Plastic
Dimension drawings:



Mounting cut-outs:



Switching positions:

