

# Switching element

46-311.1Z10

Distribution by  
Newark



<https://newark.eao.com/p/46-311.1Z10>

Your product:

---



## 46-311.1Z10 Switching element

### FRONT

**Colour:** Green

### ELECTRICAL CHARACTERISTICS

<b>Switching voltage and switching current:</b>	at AC-15				
	Voltage	24 V	120 V	240 V	600 V
	Current	10 A	6 A	3 A	1,2 A
	at DC-13				
	Voltage	24 V	120 V	240 V	
	Current	5 A	1,1 A	0,55 A	

**Thermal current I<sub>th</sub>:** 10 A (IEC-EN60947-1)

**Contacts:** 1 NO

**Pollution degree:** 3

**Insulation voltage:** U<sub>i</sub> 690V - U<sub>imp</sub> 4KV (IEC-EN60947-1)

### MECHANICAL CHARACTERISTIC

**Switching system:** Slow-make switching element

**Tightening torque:** 0.8 ... 1 Nm for screw terminal

**Terminal:** Screw terminal

**Contact material:** Silver

**Operating force:** 2 N

**Mechanical lifetime:** 1 Mio. cycles of operation

**Weight:** 0.011 kg

### AMBIENT CONDITION

**Climate resistance:** +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

**IP Protection:** IP20

**Shock resistance:** 30g, 18ms (EN-IEC 60068-2-27)  
50g, 11ms (EN-IEC 60068-2-27)

**Vibration resistance:** 5g f= 2...500Hz (EN-IEC 60068-2-6)

**Operating temperature:** - 25 °C ... + 55 °C

**CERTIFICATE**

**Approbations:** CSA, EAC, UL

**Conformities:** CE


**Standards:** CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

**OTHER**

**Material:** Plastic

**Short Description:** Switching element, Slow-make switching element, Silver, 1 NO, Screw terminal

**Wiring diagrams:**



**Dimension drawings:**

