

AS1802 1 Part Non-Corrosive Neutral Cure Adhesive Sealant (Electronic Grade)

Description

This is a non-corrosive, neutral cure, 1-part, RTV (Room Temperature Vulcanising) silicone adhesive sealant. It is one in a range of Acetone cure products which are solvent free. It exhibits excellent primerless adhesion to many substrates and cures rapidly at room temperature when in contact with atmospheric moisture to form a tough rubber. This product will not corrode copper or its alloys and is suitable for use with electronic components.

Key Features

- Excellent thermal conductivity
- Non corrosive
- Fast skinning
- Low linear shrinkage

Application

Applications include but are not limited to, automotive, thermal transfer and bonding in PCBs

Use and Cure Information

This product is a ready for use 1 Part system. If supplied in cartridges it can be applied using either manual or pneumatic dispensing guns. It can also be applied from bulk containers using conventional drum dispensing equipment.

All surfaces to which the sealant is to be applied should be clean, dry and free from grease, dirt, and loose material. Priming of surfaces is not normally required. If using as an adhesive, it should be applied to one clean surface and the other clean surface brought into contact with it within the tack free time stated opposite. For optimum bond strength, the thickness of the sealant joint should be a minimum of 1 mm.

The sealant will cure upon exposure to atmospheric moisture, ideally between 20 to 30 °C and 40% to 70% Relative Humidity. Time taken for cure will depend on the thickness of the joint, humidity and temperature. Joints should be left undisturbed for at least 24 hours, but preferably longer to effect sufficient depth of cure. Full cure requires 7 days.

“For pneumatic dispensing of 310 ml cartridges, the recommended pressure is 2.25 to 3.45 bar (40 to 50 psi). Dispensing pressure above the recommended limits may lead to gas bypassing the piston, causing spluttering at the nozzle and poor bead quality”

Health & Safety

Health and Safety

Safety Data Sheets available on request.

Packaging

CHT Adhesives are available in a variety of packaging including cartridges and bulk containers. Please contact our sales department for more information.

Users are advised to carry out their own tests on clean, degreased substrates to ensure satisfactory adhesion is achieved.

Stress cracking can appear on some grades of polycarbonate and poly(methyl methacrylate). Users are advised to carry out initial testing to ensure product compatibility.

Revision Date 29 Apr 2021
Revision No 1
Download Date 29 Jun 2024

Property

Uncured Product

Property	Test Method	Value
Appearance		Self-levelling
Cure Profile		23+/-2°C and 65% humidity
Cure Through to 3 mm Depth		8 hr
Cure Type		Acetone
Rheology		Self Level
Self Bonding		Yes
Tack Free Time / Skin Formation at 23°C/73°F		4 min
Viscosity Mixed	Brookfield	350000 cP

Cured Product

7 days at 23+/-2°C and 50+/-5% humidity

Color		Grey
Density	BS ISO 2781	2.11 g/cm3
Elongation at Break	ISO 37	103 %
Hardness Shore A	ASTM D 2240-95	67
Linear Shrinkage (%)		0.5 %
Max Working Temp		220 °C / 428 °F
Min Working Temp		-50 °C / -58 °F
Tensile Strength	ISO 37	3.9 N/mm2 / 566 psi
Thermal Conductivity		2.3 W/mK
Volume Coefficient of Thermal Expansion (ppm/°C)		493 ppm/°C

Electrical Properties

Dielectric Constant	ASTM D-150	3.85
Dielectric Strength (V/mil)		508 V/mil
Dielectric Strength kV/mm	ASTM D-149	20 kV/mm / 508 V/mil
Dissipation Factor	ASTM D-150	0.002
Volume Resistivity (Ohms cm)	ASTM D-257	1.00E+14 ohms cm

Adhesion Testing

Lap Shear Aluminium kg/cm ²	ASTM D1002	7.15 kg/cm ²
Lap Shear Copper kg/cm ²	ASTM D1002	3.6 kg/cm ²
Lap Shear Stainless Steel 304 kg/cm ²	ASTM D1002	2.98 kg/cm ²

Storage

Max Storage Temperature	40 °C / 104 °F
Shelf Life	12 mths