



Safety Data Sheet

Copyright,2023, 3M India Limited.All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

This product is defined as an article as per the Occupational Safety and Health Administration's Hazard Communication Standard (29 CFR 1910.1200(b)(6)(v)). As defined in this Standard:

'Article' means a manufactured item other than a fluid or particle: (i) which is formed to a specific shape or design during manufacture; (ii) which has end use function(s) dependent in whole or in part upon its shape or design during end use; and (iii) which under normal conditions of use does not release more than very small quantities, e.g., minute or trace amounts of a hazardous chemical, and which does not pose a physical hazard or health risk to employees.

When used under reasonable conditions and in accordance with the directions for use, the product should not present a health and safety hazard. However, use or processing of the product in a manner not in accordance with the directions for use may affect its performance and present potential health and safety hazards.

Document group:	07-5271-7	Version number:	1.00
Issue Date:	25/05/2023	Supersedes date:	Initial issue.

This Safety Data Sheet has been prepared in accordance with the GHS guidelines & India Hazardous substances (Classification, Labeling & Packaging) Draft Rules 2011.

SECTION 1: Identification

1.1. Product identifier

3M™ EMI Copper Foil Shielding Tape 1125, 1126, 1181, 1182, 1194, 1245, 2245

Product Identification Numbers

XE-0021-9589-1

1.2. Recommended use and restrictions on use

Recommended use

Electrical, Electrical insulation.

1.3. Supplier's details

Address: 3M India Limited, plot-48-51, Electronic city, Hosur road, Bangalore-560100
Telephone: 080-45543000, contact Product EHS team
E Mail: productehs.in@mmm.com
Website: <http://solutions.3mindia.co.in>

1.4. Emergency telephone number

080-45543000 (Contact hours: 8:00 AM to 5:00 PM)

SECTION 2: Hazard identification

Under MSIHC Rules, information is noted below on flammability, acute toxicity and explosivity relevant to this product. In line with international standards, information on other hazard classes and associated precautionary statements relevant to this

product are included as well.

2.1. Classification of the substance or mixture

This product is considered to be an article and is exempt from GHS classification.

2.2. Label elements

Signal Word

Not applicable.

Symbols

Not applicable

Pictograms

Not applicable

2.3. Other hazards

None known.

SECTION 3: Composition/information on ingredients

This material is a mixture.

Ingredient	CAS Nbr	% by Wt
Copper	7440-50-8	50 - 75
Acrylic polymer	9017-68-9	25 - 50
Silver-coated inert particle	None	<= 1

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation

No need for first aid is anticipated. If symptoms develop, remove the affected person to fresh air. Get medical attention.

Skin contact

If exposed, wash with soap and water. If signs/symptoms develop, get medical attention.

Eye contact

If exposed, flush eyes with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms develop, get medical attention.

If swallowed

Do not induce vomiting. Rinse mouth. If you feel unwell, get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

No critical symptoms or effects. See Section 11.1, information on toxicological effects.

4.3. Indication of any immediate medical attention and special treatment required

Not applicable

SECTION 5: Fire-fighting measures

5.1. Suitable Extinguishing media

In case of fire: Use a fire fighting agent suitable for ordinary combustible material such as water or foam to extinguish.

5.2. Special hazards arising from the substance or mixture

None inherent in this product.

Hazardous Decomposition or By-Products

Substance

Carbon monoxide.
Carbon dioxide.

Condition

During combustion.
During combustion.

5.3. Special protective actions for fire-fighters

No special protective actions for fire-fighters are anticipated.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Not applicable.

6.2. Environmental precautions

Not applicable.

6.3. Methods and material for containment and cleaning up

Not applicable.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

This product is considered to be an article which does not release or otherwise result in exposure to a hazardous chemical under normal use conditions.

7.2. Conditions for safe storage including any incompatibilities

Not applicable.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational exposure limits

If a component is disclosed in section 3 but does not appear in the table below, an occupational exposure limit is not available for the component.

Ingredient	CAS Nbr	Agency	Limit type	Additional comments
COPPER, DUSTS AND MISTS, AS CU	7440-50-8	ACGIH	TWA(as Cu dust or mist):1 mg/m3	
COPPER, FUME AS CU	7440-50-8	ACGIH	TWA(as Cu, fume):0.2 mg/m3	

ACGIH : American Conference of Governmental Industrial Hygienists

AIHA : American Industrial Hygiene Association

CMRG : Chemical Manufacturer's Recommended Guidelines

TWA: Time-Weighted-Average

STEL: Short Term Exposure Limit

CEIL: Ceiling

8.2. Exposure controls

8.2.1. Engineering controls

Not applicable.

8.2.2. Personal protective equipment (PPE)

Eye/face protection

Eye protection not required.

Skin/hand protection

PPE No chemical protective gloves are required.

Respiratory protection

None required.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	Solid.
Specific Physical Form:	Roll of Tape.
Color	Metallic Gold
Odor	Acrylic
Odour threshold	<i>Not applicable.</i>
pH	<i>Not applicable.</i>
Melting point/Freezing point: NA	<i>No data available.</i>
Boiling point/Initial boiling point/Boiling range	<i>Not applicable.</i>
Flash point	<i>Not applicable.</i>
Evaporation rate	<i>Not applicable.</i>
Flammability (solid, gas)	Not classified
Flammable Limits(LEL)	<i>Not applicable.</i>
Flammable Limits(UEL)	<i>Not applicable.</i>
Vapour pressure	<i>Not applicable.</i>
Vapor Density and/or Relative Vapor Density	<i>Not applicable.</i>
Relative density	<i>No data available.</i>
Water solubility	<i>Not applicable.</i>
Solubility- non-water	<i>Not applicable.</i>
Partition coefficient: n-octanol/water	<i>No data available.</i>
Autoignition temperature	<i>No data available.</i>
Decomposition temperature	<i>Not applicable.</i>
Viscosity/Kinematic Viscosity	<i>Not applicable.</i>
Volatile organic compounds (VOC)	0 %
Percent volatile	0 %
VOC less H ₂ O & exempt solvents	0 %

SECTION 10: Stability and reactivity

10.1 Reactivity

This material is considered to be non reactive under normal use conditions

10.2 Chemical stability

Stable.

10.3 Possibility of hazardous reactions

Hazardous polymerisation will not occur.

10.4 Conditions to avoid

None known.

10.5 Incompatible materials

None known.

10.6 Hazardous decomposition products**Substance****Condition**

None known.

Refer to section 5.2 for hazardous decomposition products during combustion.

Under recommended usage conditions, hazardous decomposition products are not expected. Hazardous decomposition products may occur as a result of oxidation, heating, or reaction with another material.

SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labelling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

11.1 Information on Toxicological effects**Signs and Symptoms of Exposure**

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation

No health effects are expected.

Skin contact

No health effects are expected.

Eye contact

No health effects are expected.

Ingestion

No health effects are expected.

Additional information:

This product, when used under reasonable conditions and in accordance with the 3M directions for use, should not present a health hazard. However, use or processing of the product in a manner not in accordance with the product's directions for use may affect the performance of the product and may present potential health and safety hazards

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

Name	Route	Species	Value
Overall product	Ingestion		No data available; calculated ATE >5,000 mg/kg
Copper	Dermal	Rat	LD50 > 2,000 mg/kg
Copper	Inhalation-Dust/Mist (4 hours)	Rat	LC50 > 5.11 mg/l
Copper	Ingestion	Rat	LD50 > 2,000 mg/kg
Acrylic polymer	Dermal		LD50 estimated to be > 5,000 mg/kg

Acrylic polymer	Ingestion	LD50 estimated to be 2,000 - 5,000 mg/kg
-----------------	-----------	--

ATE = acute toxicity estimate

Skin Corrosion/Irritation

Name	Species	Value
Copper	Rabbit	No significant irritation
Acrylic polymer	Professional judgement	No significant irritation

Serious Eye Damage/Irritation

Name	Species	Value
Copper	Rabbit	Mild irritant

Sensitization:

Skin Sensitisation

Name	Species	Value
Acrylic polymer	Professional judgement	Not classified

Respiratory Sensitisation

For the component/components, either no data are currently available or the data are not sufficient for classification.

Germ Cell Mutagenicity

For the component/components, either no data are currently available or the data are not sufficient for classification.

Carcinogenicity

For the component/components, either no data are currently available or the data are not sufficient for classification.

Reproductive Toxicity

Reproductive and/or Developmental Effects

For the component/components, either no data are currently available or the data are not sufficient for classification.

Target Organ(s)

Specific Target Organ Toxicity - single exposure

For the component/components, either no data are currently available or the data are not sufficient for classification.

Specific Target Organ Toxicity - repeated exposure

For the component/components, either no data are currently available or the data are not sufficient for classification.

Aspiration Hazard

For the component/components, either no data are currently available or the data are not sufficient for classification.

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

SECTION 12: Ecological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. Additional information leading to material classification in Section 2 is available upon request. In addition, environmental fate and effects data on ingredients may not be reflected in this section because an ingredient is present below the threshold for labelling, an ingredient is not expected to be available for exposure, or the data is considered not relevant to the material as a whole.

12.1. Toxicity

Acute aquatic hazard:

Not acutely toxic to aquatic life by GHS criteria.

Chronic aquatic hazard:

Not chronically toxic to aquatic life by GHS criteria.

No product test data available.

Material	CAS Nbr	Organism	Type	Exposure	Test endpoint	Test result
Copper	7440-50-8	Green algae	Experimental	72 hours	NOEC	0.0003 mg/l
Acrylic polymer	9017-68-9	N/A	Data not available or insufficient for classification	N/A	N/A	N/A

12.2. Persistence and degradability

Material	CAS Nbr	Test type	Duration	Study Type	Test result	Protocol
Copper	7440-50-8	Data not available-insufficient	N/A	N/A	N/A	N/A
Acrylic polymer	9017-68-9	Data not available-insufficient	N/A	N/A	N/A	N/A

12.3 : Bioaccumulative potential

Material	CAS Nbr	Test type	Duration	Study Type	Test result	Protocol
Copper	7440-50-8	Data not available or insufficient for classification	N/A	N/A	N/A	N/A
Acrylic polymer	9017-68-9	Data not available or insufficient for classification	N/A	N/A	N/A	N/A

12.4. Mobility in soil

Please contact manufacturer for more details

12.5 Other Adverse effects

No information available.

SECTION 13: Disposal considerations

13.1. Disposal methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Incinerate in a permitted waste incineration facility. As a disposal alternative, utilize an acceptable permitted waste disposal facility.

SECTION 14: Transport Information

Not hazardous for transportation.

Air Transport (IATA) Regulations

UN No Not applicable

Proper Shipping Name Not applicable

Hazard Class/Division Not applicable

Subsidiary Risk Not applicable

Packing Group: Not applicable

Marine Transport (IMDG)

UN No Not applicable

Proper Shipping Name Not applicable

Hazard Class/Division Not applicable

Subsidiary Risk Not applicable

Packing Group: Not applicable

Environmental Hazards: Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Global inventory status

Contact 3M for more information.

Applicable Environmental, Health and Safety Regulations

Hazardous Waste (Management, Handling & Transboundary) Rules, 2008

The following ingredients are listed as hazardous on Part II of Schedule I of the India Manufacture, Storage and Import of Hazardous Chemicals (MSIHC) rules

Copper

SECTION 16: Other information

NFPA Hazard Classification

Health: 0 **Flammability:** 1 **Instability:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

Revision information:

No revision information

DISCLAIMER: The information in this Safety Data Sheet (SDS) is based on our experience and is correct to the best of our knowledge at the date of publication, but we do not accept any liability for any loss, damage or injury resulting from its use (except as required by law). The information may not be valid for any use not referred to in this SDS or use of the product in combination with other materials. For these reasons, it is important that customers carry out their own evaluation to satisfy themselves as to the suitability of the product for their own intended applications. In addition, this SDS is being provided to convey health and safety information. If you are the importer of record of this product into India, you are responsible to comply with all applicable regulatory requirements, including, but not limited to, product registrations/notifications,

substance volume tracking, and potential substance registration/notification.

3M India SDSs are available at <http://solutions.3mindia.co.in>