



RoHS
Compliant

Diagram



Dimensions : Millimetres (Inches)

Item	Description	Q'ty	Materials	Treatment
1	Cover	1	Stainless Steel Dtsgmw= Nickel Silver	None
2	Stem		High - Temp Thermoplastic Nylon UL 94V-0	--
3	Adhesive Tape		Kapton	None
4	Metal Stem		Brass	Nickel Plated
5	Contact		Stainless Steel	With Silver Cladding
6	Terminal		Brass	With Silver Plating
7	Base		High - Temp Thermoplastic Nylon UL 94V-0	Molded Black



Tactile Switch

1. Style

This specification describes "Tactile Switch Washable Type", mainly used as signal switch of electric devices, with the general requirements of mechanical and electrical characteristic.

1.1 Operating Temperature Range: -25°C+70°C




1.2 Storage Temperature Range : -40°C+80°C

1.3 The shelf life of product is within 6 months.

2. Current Range: 50mA, 12V DC

3. Type of Actuation: Tactile feedback


4. **Test Sequence:**

Item	Description	Test Conditions	Requirements												
Appearance															
1	Visual Examination	By visual examination check without any out pressure & testing.	There shall be no defects that affect the serviceability of the product.												
Electric Performance															
2	Contact Resistance	Applying a static load 1.5~2 times the operating force to the center made with a 1 kHz small current contact resistance meter.	100mΩ Max.												
3	Insulation Resistance	Measurements shall be made following application of 500V DC potential across terminals and cover for 1 minute ±5 seconds	100MΩ Min.												
4	Dielectric Withstanding Voltage	250V AC(50Hz or 60Hz) shall be applied across terminals and cover for 1 minute	There shall be no breakdown or flashover.												
5	Capacitance	1 MHz ±10 kHz	5 pF max.												
6	Bounce	<p>3 to 4 operations at a rate of 1 cycles per second</p> 	<p>5 m seconds Max.</p> 												
Mechanical Performance															
7	Operating Force	<p>Applied in the direction of operation.</p> 													
			<table border="1"> <tr> <td></td> <td>65, 67, 69Y</td> <td>65, 67, 677, 69T</td> <td>66N, 677 N, 68S</td> <td>64, 65, 69, 67R</td> <td>64, 65, 69, 67N</td> </tr> <tr> <td>OF</td> <td>520±130g [5.1±.127 N]</td> <td>360±90g [3.528±.8 82N]</td> <td>160±50g [1.568±.4 9N]</td> <td>260±70g [2.548±.6 86N]</td> <td>180±50g [1.764±.4 9N]</td> </tr> </table>		65, 67, 69Y	65, 67, 677, 69T	66N, 677 N, 68S	64, 65, 69, 67R	64, 65, 69, 67N	OF	520±130g [5.1±.127 N]	360±90g [3.528±.8 82N]	160±50g [1.568±.4 9N]	260±70g [2.548±.6 86N]	180±50g [1.764±.4 9N]
	65, 67, 69Y	65, 67, 677, 69T	66N, 677 N, 68S	64, 65, 69, 67R	64, 65, 69, 67N										
OF	520±130g [5.1±.127 N]	360±90g [3.528±.8 82N]	160±50g [1.568±.4 9N]	260±70g [2.548±.6 86N]	180±50g [1.764±.4 9N]										

8	Stroke	Placing the switch such that the direction of switch operation is vertical and then gradually increasing the load applied to the stem, the stroke distance for the stem to come to a stop shall be measured.	<ol style="list-style-type: none"> 1) 0.25+0.2/-0.1mm~66N, 677N, 677T, 68S 2) 0.45±0.2mm~(64, 69, 67, 65R (N) (65T) (65, 69, 67Y) 3) 0.6±0.2mm~69, 67T
9	Stop Strength	Placing the switch such that the direction of switch operation is vertical, a static load of 3 kgf(29.4N) shall be applied in the direction of stem 7 operation for a period of 15 seconds	<ol style="list-style-type: none"> 1. As shown in item 4~7 2. Contact Resistance: 200mΩ Max 3. Insulation Resistance: 10MΩ Min
10	Solder Heat Resistance	(Through Hole Type (Soldering Temperature: 260 ±5°C (Duration of Solder Immersion: 5 ± 1 seconds. (Frequency of Soldering Process 2 times max. (PCB is 1.6mm in thickness) SMT Type ~ Series(4/4)	<ol style="list-style-type: none"> 1. Shall be free from pronounced backlash and falling-off or breakage terminals 2. As shown in item 4, 5 3. Contact Resistance: 200mΩ Max 4. Insulation Resistance: 10MΩ Min
11	Vibration	Shall be vibrated in accordance with Method 201A of MIL-STD-202F <ol style="list-style-type: none"> 1. Frequency: 10-55-10Hz in 1-min/cycle. 2. Direction: 3 vertical directions including the directions of operation 3. Test time: 2 hours each direction. 4. Swing distance=1.5mm 	<ol style="list-style-type: none"> 1. As shown in item 4~7 2. Contact Resistance: 200mΩ Max 3. Insulation Resistance: 10MΩ Min
12	Shock	Shall be shocked in accordance with Method 213B condition A of MIL-STD-202F <ol style="list-style-type: none"> 1) Acceleration: 50G 2) Action time: 11±1m seconds 3) Testing Direction: 6 sides 4) Test Cycle: 3 times in each direction 	Ditto
13	Solder ability	<ol style="list-style-type: none"> 1) Through Hole Soldering Temperature: 245±3°C 2) Lead-Free solder: M705E JIS Z 3282 A (Tin 96.5%, Silver 3%, Copper 0.5%) 3) Flux: 5~10 sec 4) Duration of solder Immersion: 5±1 sec 	No anti-soldering and the coverage of dipping into solder must more than 66% was requested.
14	Seal (Washable)	The switch is placed at a depth of 5cm in fluorocarbon FC-40 for 1 minute at 50°C	<ol style="list-style-type: none"> 1) Visually monitor the successive bubbling distance within 25mm 2) As show in item 2~5.
Seal Characteristics:			
<ol style="list-style-type: none"> 1) Do not wash immediately after soldering, do it after returning the switches back toq thermal temperature. 2) Do not apply external force to the switch during washing. 3) The switch cannot be used where subject to direct contact with water. (except for cleaning processing.) 			

Durability			
15	Operating Life	Measurements shall be made following the test forth below: 1) 5mA, 5V DC resistive load 2) Applying a static load the operating force to the center of the stem in the direction of operation 3) Static Load = OF max. 4) Cycle of Operation: 100,000 cycles~66N, 68S, 677T 500,000 cycles~67, 69, 65, 64R, N, T 300,000 cycles~65, 69, 67Y	1) As shown in item 4, 5 2) Operating force:±50% of initial force. 3) Contact Resistance: 10Ω Max 4) Insulation Resistance: 10MΩ Min 5) Bounce: 10 m seconds Max
16	Resistance Low Temperature	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for an hour before the measurements are made: 1) Temperature: -25±3°C 2) Time: 96 hours	1)As shown in item 4~7 2)Contact Resistance: 200mΩ Max 3)Insulation Resistance: 10MΩ Min
17	Resistance High Temperature	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for an hour before the measurements are made: 1)Temperature:80±2°C 2)Time:96 hours	Ditto
18	Resistance Humidity	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for an hour before the measurements are made: 1) Temperature:40±2°C 2) Relative Humidity:90~95% 3) Time:96 hours	Ditto

Soldering Conditions



- The condition mentioned above is the temperature on the Cu foil of the PCB surface.
There are cases where board's temperature greatly differs from switch's surface temperature depending on board's material, size, thickness, etc. Care, therefore, should be used not to allow switch's surface temperature to exceed 260°C.
 - Manual Soldering
- | | |
|---------------------------|----------------|
| Soldering Temperature | Max.350°C |
| Continuous Soldering Time | Max. 5 seconds |

Part Number Table

Description	Part Number
Tactile Switch, Through Hole, 6mm × 6mm, J PIN	MPDTSJW-677N-V-T/R

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.