

# 10 kV High-Voltage Oscilloscope Probe, cTUVus Listed

**CT4432**



## Features:

- 40 MHz Bandwidth
- Up to 10 kV input (DC + AC Peak)
- cTUVus safety certified
- Improved Dual Precision Resistor design
- Attenuation factor of 1000x
- Compensation range of 5 pF - 50 pF
- Replaceable tips
- Insulated BNC connection
- Use with DMM by employing BNC converter, CT3197B
- RoHS 2 Compliant
- Two-year warranty


## Description:

Because an oscilloscope has limits to the input voltage it can accept, measuring higher voltages may sometimes require the use of an attenuating high-voltage probe. The CT4432, with its improved dual precision resistor design, can accurately and safely step-down higher voltages to an acceptable level. It offers 1000x attenuation, and it features a compensation range of 5 pF to 50 pF for a wide range of oscilloscope capacitance matching.

The CT4432 High-Voltage Oscilloscope Probe enables you to safely measure voltage levels up to 10 kV. With the Cal Test Electronics name and certification by cTUVus, you can be confident this test accessory is both reliable and safe. The CT4432 is covered by a two-year warranty.

This probe is compatible with oscilloscopes (of 1 M $\Omega$  input) from all major manufacturers.

## Mechanical Drawing: Dimensions in mm, not to scale




Specifications and appearance subject to change without notice

451-073-001\_rC

[www.caltestelectronics.com](http://www.caltestelectronics.com)

**Cal Test**  
ELECTRONICS

## Diagram



### Supplied Accessories

Accessory	Model No.
Round Tip	CT2960A
Hook Tip	CT2961A
Flat Bar Tip	CT2962A
Deluxe Trimmer Tool	CT3648

Specifications and appearance subject to change without notice

451-073-001\_rC

[www.caltestelectronics.com](http://www.caltestelectronics.com)

## Order Information:

### CT4432

10 kV High-Voltage Oscilloscope Probe,  
cTUVus Listed

## Contact Info:

Toll Free: 800-572-1028 (US Only)

Phone: 714-221-9330

Fax: 714-921-9849

22820 Savi Ranch Parkway

Yorba Linda, CA 92887-4610 USA

[www.caltestelectronics.com](http://www.caltestelectronics.com)

## Specifications

Parameter	Characteristic
Maximum Input Voltage	10 kV (DC + AC Peak) 7 kV (ACrms)
Maximum Loading Current	100 $\mu$ A
Attenuation	1000x
Bandwidth	DC to 40 MHz (-3dB)
Rise Time	$\leq$ 8.8 ns
Input Resistance	100 M $\Omega$ $\pm$ 5%
Input Capacitance	2.0 pF
Accuracy	$\pm$ 3% (Below 10 kV) DC $\pm$ 3% @ 1 kHz VAC $\pm$ 3% dB 0 to 40 MHz VAC
Temperature Coefficient	$\leq$ 200 ppm/ $^{\circ}$ C
Compensation Range	5 pF to 50 pF
Alligator Clip Lead Length	1 m (3.3 ft)
BNC Cable Length	2 m (6.6 ft)
Operating Temperature	0 $^{\circ}$ C to 50 $^{\circ}$ C (32 $^{\circ}$ F to 122 $^{\circ}$ F)
Storage Temperature	-20 $^{\circ}$ C to 70 $^{\circ}$ C (-4 $^{\circ}$ F to 158 $^{\circ}$ F)
Humidity	$\leq$ 80% RH @ 40 $^{\circ}$ C (104 $^{\circ}$ F)



Copyright © 2022, Cal Test Electronics, Inc. All rights reserved.

Information in this publication supersedes that in all previously published material. Trade names referenced are the service marks, trademarks or registered trademarks of their respective companies.

Specifications and appearance subject to change without notice

451-073-001\_rC

[www.caltestelectronics.com](http://www.caltestelectronics.com)