



THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	CLASS A RELEASED	10/19/2023	B. Hansen

NOTES:

- ALL SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.
- MATERIAL:
 - MDP CONNECTOR -
 - MOLDED BODY: POLYPROPYLENE (PP), BLACK.
 - 4mm BANANA PLUGS -
 - BODY: BRASS, NICKEL PLATED.
 - CAGE CONTACT: BECU, NICKEL PLATED.
 - RG58C/U COAX CABLE -
 - JACKET: PVC, BLACK; ϕ 4.95 O.D.
 - DIELECTRIC: PE
 - CENTER CONDUCTOR: 22 AWG (19X34) TINNED COPPER, STRANDED.
 - BREAKOUT: PVC, BLACK
 - 4mm STACKING RETRACTABLE SLEEVE BANANA PLUGS -
 - BODY: BRASS, NICKEL PLATED.
 - INSULATOR (BODY): PP, COLOR SAME AS WIRE. TIP, PP, GREY.
 - CONTACT: BECU, NICKEL PLATED
- ELECTRICAL:
 - IMPEDANCE:
 - ASSEMBLY: NON-CONSTANT
 - RG58C/U: 50 Ω
 - VOLTAGE -
 - 30 VRMS / 60 VDC (HANDHELD)
 - 500 VRMS (HANDS FREE)
 - DO NOT USE ON CIRCUITS SUBJECT TO TRANSIENT OVERVOLTAGES.
 - CURRENT: 3 A MAX.
- MECHANICAL:
 - OPERATING TEMPERATURE: 0°C TO +50°C
 - CABLE BEND RADIUS:
 - REPEATED MIN. - 49.8 mm
 - ONE-TIME MIN. - 25 mm
- CE MARK:
 - ROHS 2 COMPLIANT.
 - UKCA COMPLIANT.



CT4455-100	100 ±1.5	-100
MODEL NUMBER	LENGTH & TOLERANCE (cm)	MODEL NUMBER -XXX EXTENSION

MODEL NUMBER TABLE			
THIRD ANGLE PROJECTION	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: X.X = ±0.5 X.X* = ±0.5* X.XX = ±0.25 X.XXX = ±0.125 DO NOT SCALE DRAWING	PROJECT NO. A660(b)	METRIC 22820 Savi Ranch Prky. Yorba Linda, CA 92887 USA
	MATERIAL SEE NOTES	APPROVALS DRAWN: WDH CHECKER:	TITLE CABLE ASSEMBLY, MDP TO 4mm STK RETRACTABLE SLEEVE BANANA PLUG BREAKOUTS, RG58C/U
REFERENCE	TREATMENT NONE	ENGR. B. HANSEN DESIGN ACTIVITY	DATE 10/18/2023 6/3/2021
	FINISH SEE NOTES	SIZE B	CAGE CODE 43F45
		SCALE 1:1	DWG. NO. CT4455
			REV. A
			SHEET 1 OF 1