



Axicom | Axicom Cradle Relay N


TE Internal #: 7-1393806-8

TE Internal Description: V23154C 720B104

Signal Relays: 5 Amp, Monostable DC

[View on TE.com >](#)

Relays & Contactors > Relays > Signal Relays > Signal Relays: 5 Amp, Monostable DC



Contact Voltage Rating: **150 VDC**

Coil Power Rating DC: **288 mW**

Product Mount Type: **Socket**

Contact Current Rating: **2 A**

[All Signal Relays: 5 Amp, Monostable DC \(1\)](#)

## Features

### Configuration Features

Contact Special Features	Single Contact
Contact Arrangement	4 Form C (CO)
Contact Number of Poles	2

### Electrical Characteristics

Insulation Initial Dielectric Between Open Contacts	500 Vrms
Contact Limiting Making Current	2 A
Contact Limiting Short-Time Current	2 A
Contact Limiting Continuous Current	2 A
Insulation Initial Dielectric Between Adjacent Contacts	500 Vrms
Insulation Initial Dielectric Between Contacts & Coil	1000 Vrms
Insulation Initial Resistance	1000000 MΩ
Input Voltage	125 VAC
Contact Limiting Breaking Current	2 A
Coil Resistance	550 Ω

Contact Voltage Rating	150 VDC
Coil Power Rating DC	288 mW
Contact Current Rating	2 A
Contact Switching Voltage (Max)	150 VDC

### Body Features

Product Weight	20 g[.706 oz]
----------------	---------------

### Contact Features

Contact Plating Material	Gold
Contact Material	Nickel

### Termination Features

Relay Connection Type	Plug-In
-----------------------	---------

### Mechanical Attachment

Product Mounting Feature Type	Mounting Studs
Product Mount Type	Socket

### Dimensions

Product Width	19 mm[.748 in]
Product Length	24 mm[.944 in]
Product Height	30 mm[1.18 in]

### Usage Conditions

Environmental Category of Protection	RTI
Environmental Ambient Temperature (Max)	70 °C[158 °F]
Operating Temperature Range	-40 – 70 °C

### Operation/Application

Actuating System	AC, DC
Performance Type	Standard
Coil Magnetic System	Monostable

### Packaging Features

Packaging Method	Box & Carton
------------------	--------------

### Other

Length Class (Mechanical)	20 – 25 mm
Environmental Ambient Temperature Class	50 – 70 °C

Height Class (Mechanical)	25 – 30 mm
Coil Power Rating Class	600 – 800 mW
Width Class (Mechanical)	16 – 20 mm
Contact Current Class	0 – 2 A

## Product Compliance


For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | Axicom Cradle Relay N



Signal Relays(1)

## Customers Also Bought



TE Part #102387-3  
16 MODIV HSG COMP DR .100 POL



TE Part #350429-1  
03P UMNL PIN HDR ASSY NATL



TE Part #6-1393215-7  
V23057-B0002-A101

## Documents

### CAD Files

[3D PDF](#)

[3D](#)

Customer View Model

[ENG\\_CVM\\_CVM\\_7-1393806-8\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_7-1393806-8\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_7-1393806-8\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

[Product Specification](#)

English

[Definitions General Purpose Relays](#)

English