

BA-2RV32-P405

Products > Switches > Basic Switches > Premium Large Basic Switches > BA Series > BA-2RV32-P405

Overview

MICRO SWITCH BA Series Premium Large Basic Switch, Single Pole Double Throw Circuitry, 20 A at 250 Vac, Straight Lever Actuator, 0,28 N [1.0 oz] Operating Force, Screw Termination, Silver Contacts, UL, CSA, CE, ENEC, Rigid Lev...
[View More](#)



Technical Specifications

Switch Type	MICRO SWITCH Standard 25,4 mm H x 17,8 mm W x 50,8 mm L [1.0 in H x 0.7 in W x 2.0 in L]	Ampere Rating	20 A
Sealed	No	Circuitry	SPDT
Actuator	Straight Lever	Termination	Screw
Operating Temperature	-55 °C to 85 °C [-67 °F to 185 °F]	Voltage	250 Vac
Actuator Length	31,75 mm [1.25 in]	Contact Type	Silver

[View More](#)

View documents in: English

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
MICRO SWITCH BZ/BA/BM/BE & 6AS Series Premium Large Snap-Action Switches	Datasheet	English	2MB
Oil and Gas Brochure	Brochure	English	4MB
Basic, Toggles, and Rocker Switches Range Guide	Product Range Guide	English	2MB
Safety and Productivity Solutions in Hospital Applications	Brochure	English	5MB

Product Features

- Accepted world-wide standard "Large Basic" switch
- Low operating force and differential travel
- Long mechanical life up to 20,000,000 cycles at 95% survival
- Elongated mounting hole for easier, more accurate mounting
- Current rating ranges from 15 A to 25 A
- Choice of actuation, termination and operating characteristics

Applications

- Irrigation systems
- Semi-trailer trucks
- Timing devices
- Office equipment
- Test instruments
- Medical/dental equipment
- HVAC equipment
- Manually operated devices
- Valves

view all BA-2RV32-P405 literature

view distributor inventory

sample request

email technical support

start a chat we're offline

get support

email sales

find a distributor

email this page

NAVIGATION LINKS

HOME PAGE
 PRODUCTS
 DISTRIBUTOR INVENTORY
 INDUSTRIES

DISTRIBUTOR LINKS

ECOM LOGIN
 LEARN CENTER
 REQUEST ACCESS TO ECOM
 SALES/AD PORTAL LOGIN

LANGUAGE

English

SOCIAL MEDIA



SUPPORT

NEWS & EVENTS

ABOUT US

SALES/AD PORTAL ACCESS REQUEST

SAMPLE REQUEST

SUPPLIER MICROSITE

SITE INFORMATION

PRIVACY STATEMENT

SITE MAP

TERMS & CONDITIONS

This site uses cookies to simplify and improve your usage and experience of this website. Cookies are small text files stored on the device you are using to access this website. If you ignore this message and continue without changing your browser settings, we will assume that you are consenting to our use of cookies. For further information on our use of cookies, please see our [Privacy Statement](#).

Don't show this message again