



NOTE

- 1 - TERMINALS ARE SILVER PLATED
- 2 - SWITCH IS MARKED WITH CATALOG LISTING AND DATE CODE ONLY
- 3 - RESTRICTED LISTING
- 4 - MAXIMUM MECHANICAL DEAD BREAK OF .0035 CAN BE EXPECTED WITH THIS SWITCH CONSTRUCTION

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



ELECTRICAL DATA		SCALE	FULL	SCALE PRINT
CONTACT ARRANGEMENT		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
S P D T		ONE PLACE	(.0)	±.030
		TWO PLACE	(.00)	±.015
		THREE PLACE	(.000)	±.005
CHARACTERISTICS		ANGLES		
OPERATING FORCE ----- 234 GRAMS MAX		± 3°		
RELEASE FORCE ----- 20 GRAMS MIN		WEIGHT		
DIFFERENTIAL TRAVEL ----- .014 MAX				
OVERTRAVEL ----- .037 MIN				
RELEASE TRAVEL ----- .009 MIN				

X100560-V3L

REPLACES

RELEASE NO. PR-22241

CATALOG LISTING

V3L-3352



ISSUE

2

CHECK

REVISIONS

A C095133

TSM

09JUN99

68

09JUN99

CHECK

09JUN99

JAF

CHECK

09JUN99

TSM

DRAWN

PTC/CAD 2D