

6061092-1 ✓ ACTIVE

TE Internal #: 6061092-1  
MCX RF Interface, Jack, 50  $\Omega$ , Push-On, 4 GHz Operating  
Frequency, Cable-to-Board, 1 Position, Printed Circuit Board, Panel  
Mount

[View on TE.com >](#)



Connectors > RF Connectors > Coax Connectors > MCX Connector: Jack, Vertical, 50 Ohm



RF Interface: **MCX**

RF Connector Style: **Jack**

RF Connector Mated Outer Diameter (Approximate): **4.5 mm [ .177 in ]**

Impedance: **50  $\Omega$**

RF Connector Coupling Mechanism: **Push-On**

[All MCX Connector: Jack, Vertical, 50 Ohm \(5\)](#)

## Features

### Product Type Features

RF Interface	MCX
RF Connector Style	Jack
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

### Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	1
Number of Coaxial Contacts	1

### Electrical Characteristics

Impedance	50 $\Omega$
-----------	-------------

### Body Features

Body Material	Brass
---------------	-------



Body Plating Material	Tin
-----------------------	-----

### Contact Features

RF Connector Center Contact Underplating Material	Copper, Nickel
	1397 $\mu$ m
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Beryllium Copper

### Termination Features

Termination Method to Printed Circuit Board	Surface Mount
---	---------------

### Mechanical Attachment

PCB Mount Retention	Without
RF Connector Coupling Mechanism	Push-On
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Mechanical
Detent	Without

### Dimensions

Profile Height from PCB	5.38 mm[.212 in]
Product Length	5.9 mm[.231 in]
RF Connector Mated Outer Diameter (Approximate)	4.5 mm[.177 in]

### Usage Conditions

Operating Temperature Range	-65 – 165 $^{\circ}$ C[-85 – 329 $^{\circ}$ F]
-----------------------------	--

### Operation/Application

Operating Frequency	4 GHz
---------------------	-------

### Packaging Features

Packaging Quantity	900
Packaging Method	Reel

### Other

Dielectric Material	PTFE
---------------------	------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------



EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2024 (240)

Candidate List Declared Against: JUL 2021 (219)

SVHC > Threshold:

Pb (3.7% in Component Part)

**Article Safe Usage Statements:**

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Pin-in-Paste capable to 260°C

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Customers Also Bought



TE Part #5745781-4  
D-Sub Receptacle Assembly: Right  
Angle, Shell Size 1, 2.74mm



TE Part #5227161-7  
RTANG JACK W/MTG PINS, BNC PCB



TE Part #292304-1  
STD USB TYPE B, R/A, T/H



TE Part #3-350820-2  
ULTRAFast 250 ASSY REC 16-14  
TPBR LP



TE Part #1-382811-6  
SHUNT,ECON,PHBR 15AU,BLACK L/P



TE Part #ER2166-000  
RPS-CT-50M-6.4-OUT-0



TE Part #2-1393237-8  
RT424012F

## Documents

### Product Drawings

#### OSX VERTICAL JACK

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_6061092-1\\_A.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_6061092-1\\_A.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_6061092-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### MCX Connectors

English