

1SNL340010R0000 ✓ ACTIVE

ENTRELEC

TE Internal #: 1SNL340010R0000

Power Distribution Blocks, 1 Pole, 335 A Current Rating (UL), 12

Position, DIN Rail, -55 – 110 °C [-67 – 230 °F]

[View on TE.com >](#)



Connectors > Terminal Blocks & Strips > Power Distribution Blocks > DBL Power Distribution Block: Screw clamp technology, 1 to 3 poles



Number of Poles: 1

Current Rating (IEC): 400 A

Current Rating (UL): 335 A

Number of Positions: 12

Contact Current Rating (Max): 400 A

[All DBL Power Distribution Block: Screw clamp technology, 1 to 3 poles \(12\)](#)

Features

Configuration Features

Number of Poles - Main Circuit	1
Number of Poles - Output 3	4
Number of Poles - Output 1	2
Number of Poles - Output 2	5
Number of Levels	1
Block Function	Feed-Through
Number of Circuits	1
Number of Poles	1
Number of Positions	12

Electrical Characteristics

Impulse Withstanding Voltage Rating (IEC)	8000 V
Short-Time Withstanding Current Rating @ 1s	18000 A
Operating Voltage Rating (UL & CSA) (Max) - Main Circuit	1000 V
Voltage Rating (CSA)	1000 V
Peak Withstanding Current Rating	51 kA
Voltage Rating (IEC)	1500 VDC
Power Loss	12.8 W



Short Circuit Current Rating	100 kA
Dielectric Withstanding Voltage (Max)	2200 V
Input Current (Max)	400 A
Current Rating (IEC)	400 A
Current Rating (UL)	335 A

Body Features

Primary Product Color	Gray
Product Weight	410 g[14.462 oz]

Contact Features

Contact Current Rating (Max)	400 A
------------------------------	-------

Termination Features

Termination Method to Wire & Cable	Screw
------------------------------------	-------

Mechanical Attachment

Tightening Torque - Output 1	31 – 44 in-lbs
DIN Rail Mounting Type	TH35-15, TH35-7.5
Tightening Torque - Main Circuit	221 in-lbs
Tightening Torque - Output 3	18 – 26.5 in-lbs
Tightening Torque - Output 2	18 – 26.5 in-lbs
Connector Mounting Type	DIN Rail

Housing Features

Housing Material	Polyamide
------------------	-----------

Dimensions

Output 3 Capacity - 1 Insulated Ferrule	2.5 – 10 mm ²
Output 1 Capacity - 1 Insulated Ferrule	14 – 4 AWG
Output 2 Capacity - 1 Insulated Ferrule	14 – 6 AWG
Output 2 Capacity - 1 Rigid Stranded Conductor	14 – 6 AWG
Main Circuit Capacity - 1 Rigid Stranded Conductor per Screw Clamp	168 – 400 kcmil
Hole Diameter - Output 3	5.7 mm[.224 in]
Output 3 Capacity - 1 Rigid Stranded Conductor	2.5 – 10 mm ²
Output 1 Capacity - 1 Rigid Stranded Conductor	2.5 – 35 mm ²
Tool Size - Output 3	4 mm[.157 in]

Main Circuit Capacity - 1 Insulated Ferrule per Screw Clamp	95 – 150 mm ²
Wire Stripping Length - Output 1	11 mm[.43 in]
Wire Stripping Length - Main Circuit	28 mm[1.1 in]
Tool Size - Output 2	4 mm[.157 in]
Wire Stripping Length - Output 3	11 mm[.43 in]
Hole Diameter - Output 1	8.7 mm[.342 in]
Hole Diameter - Output 2	6.5 mm[.256 in]
Tool Size - Output 1	5.5 mm[.217 in]
Hole Diameter - Main Circuit	19.8 mm[.78 in]
Wire Stripping Length - Output 2	11 mm[.43 in]
Tool Size - Main Circuit	8 mm[.315 in]
Product Spacing	46 mm[1.81 in]
Product Depth	60 mm[2.116 in]
Wire Size	150 mm ²
Product Width	46 mm[1.623 in]
Product Height	96 mm[3.386 in]

Usage Conditions

Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Industry Standards

Tool - Output 2	Flat Screwdriver
Tool - Output 1	Flat Screwdriver
Tool - Main Circuit	Allen Key
Tool - Output 3	Flat Screwdriver
IP Rating	IP10
UL Flammability Rating	UL 94V-0

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	

Current ECHA Candidate List: JAN 2024
(240)

Candidate List Declared Against: JAN 2024
(240)

SVHC > Threshold:

Pb (3.5% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1SNK140000R0000
MC512



TE Part # 1SNK900001R0000
BAM4



TE Part # 1SNK900002R0000
BAZ1



TE Part # 1SNK900102R0000
BAZH1



TE Part # 1SET111021R0000
WF160-18-IV





TE Part # 1SET111038R0000
WF100-18-RD



TE Part # 1SET111040R0000
WF160-18-BL



TE Part # 1SNK149002R0000
MC512PA L1-L2-L3-N-PE (x20) Vertical



Customers Also Bought



Documents

[CAD Files](#)

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_1SNL340010R0000_A.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_1SNL340010R0000_A.3d_igs.zip](#)

English



Customer View Model

[ENG_CVM_CVM_1SNL340010R0000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ENTRELEC DBL Power Distribution Blocks Catalogue](#)

French

[ENTRELEC DBL Power Distribution Blocks Catalogue](#)

English

[Entrelec Compact Power Block](#)

English

[ENTRELEC Terminal Block - Master Catalog](#)

[ENTRELEC Terminal Block - Master Catalog](#)

English

[DBL400](#)

English

[DBL Power-Distribution-Blocks](#)

English

[ENTRELEC Terminal Blocks Catalogue \(RUS\)](#)

[ENTRELEC Compact Power Block](#)

English

[Essential Entrelec Terminal Blocks](#)

French

[Essential Entrelec Terminal Blocks](#)

English

[Essential Entrelec Terminal Blocks](#)

Japanese

Agency Approvals

[UL](#)

English