

# DATA SHEET

## SMD 1206 SLOW BLOW FUSE JB12S Series

RoHS compliant & Halogen free



Product specification— August 10, 2023 V.0





**JB12S Series DataSheet**

**Scope**

This specification is applicable to over-current protection thick film fuse for 1206 slow blow series produced by YAGEO corporation.


**Applications**

- LCD Displays
- Battery Packs
- Hard Disk Drives

**Features**


- Small Size, 1206 SMD
- Operating temperature -55°C to 125°C
- Excellent long-term stability
- Halogen Free
- Lead Free

**Agency Approval**

Agency	File Number	Ampere Range
	E531845	0.63A-40A


**Dimensions**

Series	L (mm)	W (mm)	T (mm)	d (mm)
JB12S	3.20±0.20	1.60±0.20	0.65±0.20	0.50±0.20



**Recommended Land Patterns**

Series	L (mm)	W (mm)	D (mm)
JB12S	4.56	2.03	1.52



**Ordering Information**

Part Number	Current Rating (A)	Voltage Rating (Vdc)	Interrupting	Typical DCR (mΩ) <sup>1</sup>	Typical I <sup>2</sup> t (A <sup>2</sup> s) <sup>2</sup>	Marking
JB12S5000R	0.5A	63Vdc	50A@63Vdc	1150	0.03	0.5
JB12S6300R	0.63A			1080	0.035	B
JB12S7500R	0.75A			850	0.078	.75
JB12S1001R	1.0A			480	0.13	H
JB12S1501R	1.5A			230	0.32	K
JB12S2001R	2.0A			135	0.64	N
JB12S2501R	2.5A			75	1.28	O
JB12S3001R	3.0A			47	1.85	P
JB12S3501R	3.5A			38	2.23	R
JB12S4001R	4.0A			34	2.88	S
JB12S5001R	5.0A			24	5.16	T
JB12S6001R	6.0A			16	6.03	F
JB12S7001R	7.0A			12.3	7.24	7
JB12S8001R	8.0A			8.3	10.05	M
JB12S1002R	10A			6.5	18.20	U

**SMD 1206 Slow Blow Fuse**

**JB12S Series**

JB12S1202R	12A	48Vdc	200A@48Vdc	5	26.09	12
JB12S1502R	15A			3.7	30.56	15
JB12S2002R	20A			3.4	45.73	20
JB12S2502R	25A			1.6	69.31	25
JB12S3002R	30A			1.3	92	30
JB12S4002R	40A	36Vdc	200A@36Vdc	0.85	148	XL

NOTE:1. Measured at ≤10% rated current and 25°C  
 2. Nominal Melting I<sup>2</sup>t measured at 0.001s opening time


**Clearing Time Characteristics**

Rated Current	% of Current Rating	Clearing Time at 25°C	
		Min	Max
0.63A-40A	100%	4hours	/
	200%	1s	120s
	350%	/	3s

**Part Number Code Rule**

J	B	12	S	1001	R
Product Code	Product Type	Size Type	Fusing Type	Current Rating	Package
J:Fuse	B: Thick Film	12:1206	S: Slow Blow	6300:0.63A 1001:1A	R:Tape and Reel B: Bulk


**Temperature Derating Curve**




**SMD 1206 Slow Blow Fuse**

**JB12S Series**

**Time & Current Curve**



**I<sup>2</sup>t & Time Curve**




## Reliability Test Performance

Item	Test condition/ Methods	Performance	Standard
Time/Current Characteristics	100% Rated Current	No fusing within 4hr	UL248-14
	200% Rated Current	0.63A-40A : Min:1s;Max:120s	Refer to clearing time characteristics
	350% Rated Current	0.63A-40A : Max:3s	
Breaking Capacity	0.63A-10A: 50A@63Vdc 12A-30A: 200A@48Vdc 40A:200A@36Vdc	No a permanent arcing, ignition, bursting	UL248-14
Solderability	T=245°C±5°C, t=5s±0.5s	Cover ≥95%	MIL-STD-202 Method 208
Resistance to Soldering	Pre-heating:145°±15°C, max.120s Peak: 260°C, max.10s Reflow cycle: 2 times After immersion into solder, leaving the room temp. for 1h or more, and then measure the internal resistance.	△R<15% No crack and damage, Marking is easily legible	MIL-STD-202, Method 210F
Thermal Shock	-65°C, 15min→25°C, 5min→+125°C, 15min ; 100 cycles	△R<10% No crack and damage,	MIL-STD-202, Method 213B
Mechanical Shock	a=100G for 11ms, 5pulses	△R<10% No crack and damage	MIL-STD-202, Method 213B
Vibration	Frequency range:10~15~10Hz/min Vibration amplitude:1.5mm	△R<10% No mechanical damages	MIL-STD-202, Method 201A
Salt Spray	5% salt solution,48hr	△R<10% Legible appearance	MIL-STD-202, Method 101
Board Flex	Bending:1mm, time:60s	△R<15% No mechanical damages	IEC 60127-4


**Soldering Condition**

Recommend Re-Flowing Profile



Item	Condition
Ramp	$< 3^{\circ}\text{C/sec.}$
Pre-heating	$145 \pm 15^{\circ}\text{C}$ , 120s max.
Time above $220^{\circ}\text{C}$	60s max.
Peak temperature	$260^{\circ}\text{C}/10\text{s}$ max.

Recommend Soldering tip Temperature



Item	Condition
Iron soldering power	Max. 30W
Pre-heating time	60sec, $150^{\circ}\text{C}$
Soldering tip temperature	Max. $350^{\circ}\text{C}$
Soldering time	Max. 3sec

Note: Take care not to apply the tip of the soldering iron to the terminal electrodes.

**SMD 1206 Slow Blow Fuse**


**JB12S Series**

**Packaging Specification**


■ Quantity & Weight

Series	Quantity
JB12S	3000pcs/Reel

■ Reel & Tape Specification



Series	A (mm)	B (mm)	C (mm)	D (mm)	N (mm)	W1 (mm)	W2 (mm)
JB12S	178±5	1.6 Min.	12.8 Min.	20.8 Min.	58±2	8.4 Min.	12.4 Max.




Series	A0 (mm)	B0 (mm)	D0 (mm)	D1 (mm)	E2 (mm)	F (mm)	K0 (mm)
JB12S	1.92±0.10	3.62±0.10	1.50 <sup>+0.1</sup>	1.00 min.	1.75±0.10	3.50±0.05	0.87±0.10
	P0 (mm)	P1 (mm)	P2 (mm)	T (mm)	W (mm)	$\theta$ (mm)	
	4.00±0.10	4.00±0.10	2.00±0.05	0.25±0.05	8.00±0.30	6° max.	



**■ Peeling Strength of Seal Tape**

The top cover tape is pulled at a speed of 300 mm/min with the angle between the tape during peel and the direction of unreeling maintained at 165 to 180 degree as following picture. The peel force of paper carrier tape shall be 0.1N to 0.7N(10 to 70 g)

**Storage Conditions**

- Storage Temperature: 10°C~+40°C
- Relative Humidity: ≤75%RH
- Keep away from corrosive atmosphere and sunlight.
- Period of Storage: 2 year.

## LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial, automotive, and/or COTS grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.