



## Voluntary safety information based on the Safety Data Sheet in accordance with Annex II of Regulation (EC) No 1907/2006

Page 1 of 8

SDS No. : 640978

V001.1

BERGQUIST GAP PAD TGP 2200SF known as Gap Pad 2200SF

Revision: 29.09.2022

printing date: 24.05.2024

Replaces version from: 18.02.2019

### SECTION 1: Identification of the article and of the company/undertaking

#### 1.1. Product identifier

BERGQUIST GAP PAD TGP 2200SF known as Gap Pad 2200SF

#### 1.2. Relevant identified uses of the article and uses advised against

Intended use:

Thermal Interface Material

#### 1.3. Details of the supplier of the safety data sheet

Henkel AG & Co. KGaA

Henkelstr. 67

40589 Düsseldorf

Germany

Phone: +49 211 797 0

SDSinfo.Adhesive@henkel.com

For Safety Data Sheet updates please visit our website <https://mysds.henkel.com/index.html#/appSelection> or [www.henkel-adhesives.com](http://www.henkel-adhesives.com).

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the article

##### Classification (CLP):

Substances and preparations marketed in a specific form or within specific containers need not to be classified according to the REACH Regulation Article 3 (3).

#### 2.2. Label elements

##### Label elements (CLP):

Substances and preparations marketed in a specific form or within specific containers need not to be classified according to the REACH Regulation Article 3 (3).

#### 2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

**Following substances are present in a concentration  $\geq 0,1\%$  and fulfill the criteria for PBT/vPvB, or were identified as endocrine disruptor (ED):**

This mixture does not contain any substances in concentration  $\geq$  the concentration limit that are assessed to be a PBT, vPvB or ED.

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

**General chemical description:**

Manufactured item - article

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Contains no Substances of Very High Concern or Skin Sensitising Substances exceeding the limits of the relevant EU Regulation.

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

**Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

**Skin contact:**

Rinse with running water and soap.

Obtain medical attention if irritation persists.

**Eye contact:**

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

**Ingestion:**

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

**Suitable extinguishing media:**

water, carbon dioxide, foam, powder

**Extinguishing media which must not be used for safety reasons:**

High pressure waterjet

#### 5.2. Special hazards arising from the article

Silicon dioxide

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO<sub>2</sub>) and nitrogen oxides (NO<sub>x</sub>) can be released.

In case of fire, keep containers cool with water spray.

#### 5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

**Additional information:**

In case of fire, keep containers cool with water spray.

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin and eyes.

Wear protective equipment.

Ensure adequate ventilation.

**6.2. Environmental precautions**

Do not empty into drains / surface water / ground water.

**6.3. Methods and material for containment and cleaning up**

Scrape up as much material as possible.

Sweep up spilled material. Avoid creating dust.

Keep in suitable and closed containers for disposal.

**6.4. Reference to other sections**

See advice in section 8

**SECTION 7: Handling and storage****7.1. Precautions for safe handling**

Avoid skin and eye contact.

See advice in section 8

Hygiene measures:

Good industrial hygiene practices should be observed.

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

**7.2. Conditions for safe storage, including any incompatibilities**

Ensure good ventilation/extraction.

Keep container tightly sealed.

Refer to Technical Data Sheet

**7.3. Specific end use(s)**

Thermal Interface Material

**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Occupational Exposure Limits**

Valid for

Great Britain

None

**Occupational Exposure Limits**

Valid for

Ireland

None

**Biological Exposure Indices:**

None

**8.2. Exposure controls:**

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

**Hand protection:**

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

**Eye protection:**

Wear protective glasses.

Protective eye equipment should conform to EN166.

**Skin protection:**

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

**Advices to personal protection equipment:**

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Physical state	solid
Delivery form	solid
Colour	green
Odor	slightly
Melting point	Not applicable, Decomposes.
Solidification temperature	Not applicable, Product is a solid.
Initial boiling point	< 200 °C (< 392 °F)
Flammability	The product is not flammable.
Explosive limits	Not applicable, Product is a solid.
Flash point	Not applicable, Product is a solid.
Auto-ignition temperature	Not applicable, Product is a solid.
Decomposition temperature	Not applicable, Substance/mixture is not self-reactive, no organic peroxide and does not decompose under foreseen conditions of use
pH	Not applicable, Product is non-soluble (in water).
Viscosity (kinematic)	Not applicable, Product is a solid.
Solubility (qualitative)	Currently under determination
Partition coefficient: n-octanol/water	Not applicable
	Mixture
Vapour pressure (20 °C (68 °F))	< 1 hPa
Density	Currently under determination
Relative vapour density:	Not applicable, Product is a solid.
Particle characteristics	Not applicable Product is not powder.

**9.2. Other information**

Other information not applicable for this product

**SECTION 10: Stability and reactivity****10.1. Reactivity**

None.

**10.2. Chemical stability**

Stable under recommended storage conditions.

**10.3. Possibility of hazardous reactions**

See section reactivity

**10.4. Conditions to avoid**

Stable under normal conditions of storage and use.

**10.5. Incompatible materials**

See section reactivity.

**10.6. Hazardous decomposition products**

carbon oxides.

**SECTION 11: Toxicological information****1.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008****Acute oral toxicity:**

No data available.

**Acute dermal toxicity:**

No data available.

**Acute inhalative toxicity:**

No data available.

**Skin corrosion/irritation:**

No data available.

**Serious eye damage/irritation:**

No data available.

**Respiratory or skin sensitization:**

No data available.

**Germ cell mutagenicity:**

No data available.

**Carcinogenicity**

No data available.

**Reproductive toxicity:**

No data available.

**STOT-single exposure:**

No data available.

**STOT-repeated exposure::**

No data available.

**Aspiration hazard:**

No data available.

**11.2 Information on other hazards**

not applicable

**SECTION 12: Ecological information**

**12.1. Toxicity**

**Toxicity (Fish):**

No data available.

**Toxicity (Daphnia):**

No data available.

**Chronic toxicity to aquatic invertebrates**

No data available.

**Toxicity (Algae):**

No data available.

**Toxicity to microorganisms**

No data available.

**12.2. Persistence and degradability**

No data available.

**12.3. Bioaccumulative potential**

No data available.

**12.4. Mobility in soil**

No data available.

**12.5. Results of PBT and vPvB assessment**

This mixture does not contain any substances that are assessed to be a PBT or vPvB.

**12.6. Endocrine disrupting properties**

not applicable

**12.7. Other adverse effects**

No data available.

**SECTION 13: Disposal considerations****13.1. Waste treatment methods**

Product disposal:

Do not empty into drains / surface water / ground water.

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

Dispose of in accordance with local and national regulations.

**SECTION 14: Transport information****14.1. UN number or ID number**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.2. UN proper shipping name**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.3. Transport hazard class(es)**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.4. Packing group**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.5. Environmental hazards**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.6. Special precautions for user**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.7. Maritime transport in bulk according to IMO instruments**

not applicable

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the article**

VOC content < 0 %  
(2010/75/EC)

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

**SECTION 16: Other information**

ED:	Substance identified as having endocrine disrupting properties
EU OEL:	Substance with a Union workplace exposure limit
EU EXPLD 1:	Substance listed in Annex I, Reg (EC) No. 2019/1148
EU EXPLD 2	Substance listed in Annex II, Reg (EC) No. 2019/1148
SVHC:	Substance of very high concern (REACH Candidate List)
PBT:	Substance fulfilling persistent, bioaccumulative and toxic criteria
PBT/vPvB:	Substance fulfilling persistent, bioaccumulative and toxic plus very persistent and very bioaccumulative criteria
vPvB:	Substance fulfilling very persistent and very bioaccumulative criteria

**Further information:**

This Voluntary safety information has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (SDSinfo.Adhesive@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the article in the state in which it is delivered. It is intended to describe our articles from the point of view of safety requirements and is not intended to guarantee any particular properties.

**Relevant changes in this voluntary safety information are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**