



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.064 ohms ±10%
D.C. RESISTANCE	3-4 @20°C	0.051 ohms ±10%
D.C. RESISTANCE	5-7 @20°C	0.023 ohms ±10%
D.C. RESISTANCE	6-8 @20°C	0.032 ohms ±10%
INDUCTANCE	3-4 10kHz, 100mVAC, 1s	24.0uH ±10%
LEAKAGE INDUCTANCE	3-4 tie(1+2, 5+8+7+8), 100kHz, 100mVAC, 1s	500nH max.
DIELECTRIC RATING	1-8 tie(2+3, 5+6), 1875VAC, 1 second	1500VAC, 1 minute
TURNS RATIO	(3-4):(5-7) 4:1, ±2%	
TURNS RATIO	(3-4):(6-8) 4:1, ±2%	
TURNS RATIO	(3-4):(2-1) 4:1, ±2%	




REV.	DATE
6A	9/08
6B	12/08

Packaging Specifications
 Method: Tape & Reel
 PKG-0328
 www.midcom-inc.com

Unless otherwise specified:
 Tolerances:
 Angles: ±1°
 Fractions: ±1/64
 Decimals: ±.005[.127]
 This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE
TRANSFORMER
 eISos p/n: 750310559



DRAWING NO.
750310559
 REVISIONS: SEE SHEET 1
 SCALE ---
 SHEET 2 OF 5