




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes




ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.48 ohms max.
D.C. RESISTANCE	3-4 @20°C	0.050 ohms max.
D.C. RESISTANCE	5-7 @20°C	0.100 ohms max.
D.C. RESISTANCE	6-8 @20°C	0.100 ohms max.
INDUCTANCE	3-4 100kHz, 100mVAC, Ls	15uH ±10%
LEAKAGE INDUCTANCE	3-4 tie(1+2, 5+6+7+8), 100kHz, 100mVAC, Ls	250nH typ., 600nH max.
DIELECTRIC	3-5 tie(2+4, 6+7), 1875VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(3-4):(5-7)	1:1, ±1%
URNS RATIO	(3-4):(6-8)	1:1, ±1%
URNS RATIO	(3-4):(2-1)	1:1, ±1%


TERM. NO.'s FOR REF. ONLY



LOT CODE & DATE CODE



AREA REPRESENTS TERMINAL PAD DIMENSIONS



REV.	DATE
6B	1/09
6A	12/08

Packaging Specifications
 Method: Tape & Reel
 PKG-0193
 www.midcom-inc.com

Unless otherwise specified:
 Tolerances: Fractions: ±1/64
 Angles: ±1° Decimals: ±.005[.127]

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE

TRANSFORMER

eiSos p/n: 750370042



DRAWING NO.

750370042

REVISIONS: SEE SHEET 1

SCALE ---

SHEET 2 OF 5