




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

D.C. RESISTANCE (@20°C):	7-8 (tie 4+5+6+7, 8+9+10+11), 0.005 Ohms max. 1-3, 0.250 Ohms max. (.120 typ.)
DIELECTRIC RATING:	1000VAC, 1 minute tested by applying 1250VAC for 1 second between PRI - SEC
INDUCTANCE:	2.5µH ±10%, 50kHz, 10mVAC, 0mADC, 7-8(tie 4+5+6+7, 8+9+10+11), Ls.
LEAKAGE INDUCTANCE:	100nH max., 100KHz, 1.0VAC, 7-8(tie 1+3, 4+5+6+7, 8+9+10+11), Ls.
URNS RATIO:	(13-3):(1-13), (1):(1.00), ±1%. (1-3):(4-11), (10):(1.00), ±1%. (1-3):(5-10), (10):(1.00), ±1%. (1-3):(6-9), (10):(1.00), ±1%. (1-3):(7-8), (10):(1.00), ±1%.

T_0_4473

Midcom, Inc. Watertown, SD USA Toll Free: 800-643-2661 Fax: 605-886-4486	Unless otherwise specified, tolerances are as follows: Angles: ±1° Fractions: ±1/64 Decimals: ±.005(.127mm)		Midcom, Inc.	
	Drawing Title Transformer		Drawing Number 750310355	Rev. 00
This drawing is dual dimensioned. Dimensions in brackets are in millimeters	Revisions: See Sheet 1		Scale ----	Sheet 2 of 5
Engineer:APS			10/30/2007	