Unscreened Multicore Cable 3 Core





RoHS Compliant

Description

0.2mm² Stranded PACW, 3 Cores, PVC Insulation, PVC Sheath.

Application

Power supply wire, suitable for indoor small electrical instrument, or general in portable tool.

Construction

Conductor

Material : Plain Annealed Copper Wire

Size : 0.2mm²

Construction : Stranded (18/0.12mm)

Insulation

Material : PVC Nominal O.D : 1.5mm

Colour : Blue, Brown, Yellow/Green Stripe

Sheath

Material : PVC
Nominal O.D : 5.3mm
Colour : Black

Physical Properties

Min. Bend Radius : 31mm

Operating Temperature : -15°C to +70°C

Electrical Properties

Rated Voltage : 48V AC (not for power applications)

Max. Conductor DC Resistance

@ 20° C : 88.2Ω /km Max. Current Rating : 1A

Voltage Test : Core to Core 1kV AC/1min

Part Number Table

Description	Part Number
Multicore Cable, Unscreened, 3 Core, 0.22mm ²	15/X/11 BLACK 1A

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

