

ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION

Part Number: 5314C
Page 1 of 1 Pages

Issue: 10
Issue Date: 1/29/2008
Effective Date: 3/1/2008

A. Construction

Diameters (In)

- 1) Component 1 19 X 1 COND
- a) Conductor 22 (7/30) AWG TC
- b) Insulation 0.010" Wall, Nom. PVC, Semi Rigid 0.050
- (1) Color Code Alpha Wire Company Color Code E

Cond	Color	Cond	Color	Cond	Color
1	BLACK	8	VIOLET	15	WHITE/YELLOW
2	BROWN	9	SLATE	16	WHITE/GREEN
3	RED	10	WHITE	17	WHITE/BLUE
4	ORANGE	11	WHITE/BLACK	18	WHITE/VIOLET
5	YELLOW	12	WHITE/BROWN	19	WHITE/SLATE
6	GREEN	13	WHITE/RED		
7	BLUE	14	WHITE/ORANGE		

- 2) Cable Assembly 19 Components Cabled
- a) Twists: 4.0 Twists/foot (min)
- b) Core Wrap Nonwoven Polyester Tape, 25% Overlap, Min.
- 3) Shield: A/P/A Tape, 25% Overlap, Min.
- a) Drain Wire 22 (7/30) AWG TC
- b) Braid TC, 70% Coverage, Min.
- 4) Jacket 0.063" Wall, Nom., PVC 0.408 (0.428 Max.)
- a) Color(s) Slate, Black, Yellow, Orange, Blue, Green, Red, Sand Beige, White
- b) Ripcord 1 End 810 Denier Nylon
- c) Print ALPHA WIRE-* P/N 5314C 19C 22 AWG

XTRAGUARD 1 XTREME PERFORMANCE FOR XTREME ENVIRONMENTS - SHIELDED 105C (UL) TYPE CM OR AWM 2343 VW-1 --- LLXXXXXX CSA 105C TYPE CMG FT4 CE ROHS <SEQ FOOTAGE>

* = Factory Code

[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]

B. Industry Approvals

- 1) UL
 - a) Component 1 AWM/STYLE 10002 105°C / 300 VRMS
 - b) Overall AWM/STYLE 2343 80°C
 - CM 105°C
 - VW-1
- 2) CSA International CMG 105°C
- FT4
- 3) EU Directive 2002/95/EC(RoHS):

All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.

- 4) California Proposition 65: The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.
- 5) CE: LVD 73/23/EEC Amendment 93/68/EEC

C. Physical & Mechanical Properties

- 1) Temperature Range -20 to 105°C
- 2) Bend Radius 10X Cable Diameter
- 3) Pull Tension 115 Lbs, Maximum
- 4) Sunlight Resistance Yes

D. Electrical Properties

- (For Engineering purposes only)
- 1) Voltage Rating 300 VRMS

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION

Part Number: 5314C
Page 2 of 1 Pages

Issue: 10
Issue Date: 1/29/2008
Effective Date: 3/1/2008

- | | |
|-----------------------|---|
| 2) Capacitance | 36 pf/ft @1 kHz, Nominal Conductor to Conductor |
| 3) Ground Capacitance | 65 pf/ft @1 kHz, Nominal |
| 4) Inductance | 0.18 μ H/ft, Nominal |
| 5) Conductor DCR | 16.6 Ω /1000ft @20°C, Nominal |
| 6) OA Shield DCR | 2.7 Ω /1000ft @20°C, Nominal |

E. Other

- 1) Packaging
 - a) 1000 FT
 - b) 500 FT
 - c) 100 FT
 - d) Bulk(Made-to-order)

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.