

INTRODUCTION

This product is a driver-free camera with 0.3MP (MegaPixels) and 640*480 resolution. The camera is well compatible with both [Raspberry Pi](#) and [NVIDIA](#) series mainboards. Just plug it in, and you're good to go!

The compact size of 30*25*21.4mm makes the module possible to be embedded in a variety of devices, which can be used for applications like face identification, image recognition, security and protection, and remote teaching.

SPECIFICATION

- Photosensitive Element: CMOS
- AGC/AEC/AWB: auto
- Infrared Filter: 650±10nm
- Supports MJPG and YUV format
- FPN: < 0.03% of VPEAK-TO-PEAK
- Connector: USB 2.0
- Pixel: 30W
- Resolution: 640*480
- Operating Voltage: 5V
- Operating Temperature: -20~70
- Dimension: 30*25*21.4mm/1.18*0.98*0.84"
- Supports Windows, iOS, Android, Linux

PROJECTS

Project 1. [Top 10 Worth of Trying Raspberry Pico/Pi 4/Pi 3B+ Projects](#)



Project 2. [30 Awesome Projects for a Raspberry Pi](#)



SHIPPING LIST

- USB Camera for Raspberry Pi and NVIDIA x1