

Sauls Wharf House Crittens Road Great Yarmouth Norfolk NR31 0AG Telephone +44 (0)1493 602602 Email:sales@midasdisplays.com Email:tech@midasdisplays.com www.midasdisplays.com

MD21605B6W-FPTLWI3 2 x 16		3.79mm Character Height	LCD Module			
Specification						
Version: 1		Date: 01/08/2020				
	Revision					
1	29/07/2020	First Issue				

Display F	eatures		
Character Count	2 x 16		
Appearance	Black on White		
Logic Voltage	3V		
Interface	I2C		1
Font Set			CHS
Display Mode	Transflective		ROHS ompliant
Character Height	3.79mm	0	ompliant
LC Type	FSTN		
Module Size	66.00 x 28.00 x 9.30 mm		
Operating Temperature	-20°C ~ +70°C		
Construction	СОВ	Box Quantity	Weight / Display
LED Backlight SIGN	MANUFACTWhite	RE -SUP	PLY

* - For full design functionality, please use this specification in conjunction with the ST7032i specification. (Provided Separately)

Disp	Display Accessories				
Part Number	Description				

Optional Variants					
Fonts	Appearances	Voltage			
		3V			

General Specification

The Features is described as follow:

■ Number of Characters: 16 characters x 2 Lines

■ Module dimension: 66.0 x 28.0 x 9.3 mm

■ View area: 40.0 x 9.98 mm

■ Active area: 38.0 x 7.98 mm

■ Dot size: 0.36 x 0.43 mm

■ Dot pitch: 0.41 x 0.48 mm

■ Character size2.00 x 3.79 mm

■ Character pitch2.40 x 4.19 mm

■ LCD type: FSTN Positive Transflective

■ Duty: 1/16 , 1/5 Bias

■ View direction: 6 o'clock


■ Backlight Type: LED White MANUFACTURE • SUPPLY

■ IC: ST7032i

Interface Pin Function

Pin No.	Symbol	Level	Description
1	VDD	Р	Power supply
2	VSS	Р	Ground
3	SDA	-	(In I2C interface DB7 (SDA) is input data. SDA and SCL must connect to I2C bus (I2C bus is to connect a resister between SDA/SCL and the power of I2C bus).
4	SCL	-	(In I2C interface DB6 (SCL) is clock input. SDA and SCL must connect to I2C bus (I2C bus is to connect a resister between SDA/SCL and the power of I2C bus).
5	RST	-	RESET (Low active)
6	А	-	LED+
7	К		LED-
8	NC	-	No Connection

Contour Drawing




Optical Characteristics

Item	Symbol	Condition	Min	Тур	Max	Unit
	θ	CR≧2	0	_	30	ψ= 180°
	θ	CR≧2	0	_	60	ψ= 0°
View Angle	θ	CR≧2	0	_	45	ψ= 90°
	θ	CR≧2	0	_	45	ψ= 270°
Contrast Ratio	CR	_	_	5	_	_
D	T rise	_	_	150	200	ms
Response Time	T fall	_	_	150	200	ms








Intensity

Conditions:

Frame Frequency: 64 HZ Driving Waveform: 1/N duty, 1/a bias

Definition of viewing angle(CR≧2)



Absolute Maximum Ratings

Item	Symbol	Min	Тур	Max	Unit
Operating Temperature	Тор	-20	_	+70	°C
Storage Temperature	Тѕт	-30	_	+80	°C
Input Voltage	Vin	-0.3	_	V _{DD} +0.3	V
Power Supply Voltage	V _{DD} -V _{SS}	-0.3	_	+6.0	V
LCD Driver Voltage	V _{LCD}	2.7	_	7.0	V

Electrical Characteristics

Item	Symbol	Condition	Min	Тур	Max	Unit
Supply Voltage For Logic	V _{DD} -V _{SS}	PL	3	3.3	3.5	V
		Ta=-20℃	_	_	_	V
Supply Voltage For LCD	VLCD	Ta=25℃	4.3	4.5	4.7	V
DESIGN	• MAI	Ta=70℃	TURE	•_SL	IPPLY	V
Input High Volt.	ViH	_	0.7 V _{DD}	_	V _{DD}	V
Input Low Volt.	VIL	_	_	_	0.2 V _{DD}	V
Output High Volt.	V _{OH}	_	0.8 V _{DD}	_	V_{DD}	V
Output Low Volt.	V _{OL}	_	_	_	0.2V _{DD}	V
Supply Current(No						
include	IDD	_	_	0.2	1	mA
LED Backlight)						

Note1: Please kindly consider to design the Vop to be adjustable while programing the software to match LCD contrast tolerance.


Backlight Information

Specification

Parameter	Symbol	Min	Тур	Max	Unit	Test Condition
Supply Current	ILED	10	32	40	mA	V=3.5V
Supply Voltage	V	3.4	3.5	3.6	V	ILED=32mA
Reverse Voltage	VR	_	_	5	V	_
Colour	Х	0.27	0.29	0.31	_	II FD=22 A
Coordinate	Y	0.28	0.30	0.32	_	ILED=32mA
Luminance (Without LCD)	IV	1080	1350	_	cd/m²	ILED=32mA
LED Life Time					7	ILED=32mA
(For Reference			50K	_	Hr.	25℃,50-60%RH,
only)		9			—)	(Note 1)
Color	White					

Note: The LED of B/L is drive by current only, drive voltage is for reference only. drive voltage can make driving current under safety area (current between minimum and maximum).

Note 1:50K hours is only an estimate for reference.



Reliability

Content of Reliability Test (Wide temperature, -20°c~70°C)

Environmental Test							
Test Item	Content of Test	Test Condition	Note				
High Temperature storage	Endurance test applying the high storage temperature for a long time.	80°C 200hrs	2				
Low Temperature storage	Endurance test applying the low storage temperature for a long time.	-30°C 200hrs	1,2				
High Temperature Operation	Endurance test applying the electric stress (Voltage & Current) and the thermal stress to the element for a long time.	70°C 200hrs					
Low Temperature Operation	Endurance test applying the electric stress under low temperature for a long time.	-20°C 200hrs	1				
High Temperature/ Humidity storage	The module should be allowed to stand at 60°C,90%RH max For 96hrs under no-load condition excluding the polarizer, Then taking it out and drying it at normal temperature.	60°C,90%RH 96hrs	1,2				
Thermal shock resistance	The sample should be allowed stand the following 10 cycles of operation -20°C 25°C 70°C 30min 5min 30min 1 cycle	-20°C/70°C 10 cycles					
Vibration test DESIGN	Endurance test applying the vibration during transportation and using.	Total fixed amplitude: 1.5mm Vibration Frequency: 10~55Hz One cycle 60 seconds to 3 directions of X,Y,Z for Each 15 minutes	3				
Static electricity test	Endurance test applying the electric stress to the terminal.	VS=±600V(contact), ±800v(air), RS=330 Ω CS=150pF 10 times					

Note1: No dew condensation to be observed.

Note2: The function test shall be conducted after 4 hours storage at the normal Temperature and humidity after remove from the test chamber.

Note3: The packing have to including into the vibration testing.

Inspection specification

NO	Item		Criterion		AQL
01	Electrical Testing	 1.1 Missing vertical, horizont defect. 1.2 Missing character, dot of 1.3 Display malfunction. 1.4 No function or no display 1.5 Current consumption excess 1.6 LCD viewing angle defect 1.7 Mixed product types. 1.8 Contrast defect. 	or icon. y. ceeds product spe ct.	ecifications.	0.65
02	Black or white spots on LCD (display only)	2.1 White and black spots on display ≤0.25mm, no more than three white or black spots present.2.2 Densely spaced: No more than two spots or lines within 3mm			
03	LCD black spots, white spots, contamination (non-display)	3.2 Line type : (As following Length $\frac{\mathbf{w}}{\mathbf{L}} = \frac{\mathbf{w}}{\mathbf{L}} = \frac{\mathbf{L} \leq 3.0}{\mathbf{L}} = \frac{0.2}{2.5}$	$Φ \le 0.10$ $10 < Φ \le 0.20$ $20 < Φ \le 0.25$ $25 < Φ$	Acceptable Q TY Accept no dense 2 1 0 Acceptable Q TY Acceptable Q TY Accept no dense 2 As round type	2.5
04	Polarizer bubbles	to find, must check in	Size Φ $Φ \le 0.20$ $0.20 < Φ \le 0.50$ $0.50 < Φ \le 1.00$ $1.00 < Φ$ Total Q TY	Acceptable Q TY Accept no dense 3 2 0 3	2.5

NO	Item	Criterion				
05	Scratches	Follow NO.3 LCD black	spots, white spots, con	tamination		
		Symbols Define: x: Chip length k: Seal width t: Cl L: Electrode pad length 6.1 General glass chip 6.1.1 Chip on panel sur x: Chip thickness Z≤1/2t 1/2t <z≤2t< td=""><td>spots, white spots, conf Chip width z: Chip to Glass thickness a: LCD</td><td>thickness 0 side length panels: x: Chip length x≤ 1/8a x≤ 1/8a</td><td>2.5</td></z≤2t<>	spots, white spots, conf Chip width z: Chip to Glass thickness a: LCD	thickness 0 side length panels: x: Chip length x≤ 1/8a x≤ 1/8a	2.5	
		1/2t < z ≤ 2t	Not exceed 1/3k	x≦1/8a		
		⊙ If there are 2 or more	chips, x is the total leng	yth of each chip.		

NO	Item	Criterion						
		Symbols: x: Chip length y: Chip width z: Chip thickness k: Seal width t: Glass thickness a: LCD side length L: Electrode pad length 6.2 Protrusion over terminal: 6.2.1 Chip on electrode pad:						
		y: Chip width x: Chip length z: Chip thickness						
		y≦0.5mm	x≦1/8a	$0 < z \le t$				
		6.2.2 Non-conductive portion:						
				. 1				
	01							
06	Glass	- NOTE OF			2.5			
	Clack	ack y Z						
		X		Х				
	DES	v: Chip width	x: Chip length z	·· Chip thickness				
	Des	y≦ L	x≤1/8a	$0 < z \le t$				
		 ✓ If the chipped area touches the ITO terminal, over 2/3 of the ITO must remain and be inspected according to electrode terminal specifications. 						
		⊙ If the product will be heat sealed by the customer, the alignment						
		mark not be damaged.						
		6.2.3 Substrate protuberance and internal crack.						
		X	y: width	x: length				
		x ≤ a						
		$y \le 1/3L$ $x \le a$						

NO	Item	Criterion				
07	Cracked glass	The LCD with extensive crack is not acceptable.				
08	Backlight elements	 8.1 Illumination source flickers when lit. 8.2 Spots or scratched that appear when lit must be judged. Using LCD spot, lines and contamination standards. 8.3 Backlight doesn't light or color wrong. 				
09	Bezel	9.1 Bezel may not have rust, be deformed or have fingerprints, stains or other contamination.9.2 Bezel must comply with job specifications.	2.5 0.65			
		 10.1 COB seal may not have pinholes larger than 0.2mm or contamination. 10.2 COB seal surface may not have pinholes through to the IC. 10.3 The height of the COB should not exceed the height indicated in the assembly diagram. 10.4 There may not be more than 2mm of sealant outside the seal area on the PCB. And there should be no more than three places. 				
10	PCB · COB	 10.5 No oxidation or contamination PCB terminals. 10.6 Parts on PCB must be the same as on the production characteristic chart. There should be no wrong parts, missing parts or excess parts. 10.7 The jumper on the PCB should conform to the product 				
	Design	characteristic chart. 10.8 If solder gets on bezel tab pads, LED pad, zebra pad or screw hold pad, make sure it is smoothed down.	0.65			
		10.9 The Scraping testing standard for Copper Coating of PCB X * Y<=2mm2	2.5			
11	Soldering	 11.1 No un-melted solder paste may be present on the PCB. 11.2 No cold solder joints, missing solder connections, oxidation or icicle. 11.3 No residue or solder balls on PCB. 11.4 No short circuits in components on PCB. 	2.5 2.5 2.5 0.65			

NO	Item	Criterion			
		12.1 No oxidation, contamination, curves or, bends on interface Pin (OLB) of TCP.			
		12.2 No cracks on interface pin (OLB) of TCP.			
		12.3 No contamination, solder residue or solder balls on product.	2.5		
		12.4 The IC on the TCP may not be damaged, circuits.			
		12.5 The uppermost edge of the protective strip on the interface			
		pin must be present or look as if it cause the interface pin to			
	General	sever.			
12	appearance	12.6 The residual rosin or tin oil of soldering (component or chip			
		component) is not burned into brown or black color.	2.5		
		12.7 Sealant on top of the ITO circuit has not hardened.12.8 Pin type must match type in specification sheet.			
		12.9 LCD pin loose or missing pins.			
		12.10 Product packaging must the same as specified on			
		packaging specification sheet.			
	_	12.11 Product dimension and structure must conform to product			
		specification sheet.			
		12.12 Visual defect outside of VA is not considered to be rejection.			

DESIGN • MANUFACTURE • SUPPLY

Precautions in use of LCD Modules

- (1)Avoid applying excessive shocks to the module or making any alterations or modifications to it.
- (2)Don't make extra holes on the printed circuit board, modify its shape or change the components of LCD module.
- (3)Don't disassemble the LCM.
- (4)Don't operate it above the absolute maximum rating.
- (5)Don't drop, bend or twist LCM.
- (6) Soldering: only to the I/O terminals.
- (7)Storage: please storage in anti-static electricity container and clean environment.
- (8) Midas have the right to change the passive components, including R3,R6 & backlight adjust resistors. (Resistors, capacitors and other passive components will have different appearance and color caused by the different supplier.)
- (9) Midas have the right to change the PCB Rev. (In order to satisfy the supplying stability, management optimization and the best product performance...etc, under the premise of not affecting the electrical characteristics and external dimensions, Midas have the right to modify the version.)
- (10) To ensure the stability of the display screen, please apply screen saver after showing 30 mins of fixed display content.
- (11)Please heat up a little the tape sticking on the components when removing it; otherwise the components might be damaged.

DESIGN • MANUFACTURE • SUPPLY

Material List of Components for RoHs

1. Midas Displays hereby declares that all of or part of products (with the mark "#"in code), including, but not limited to, the LCM, accessories or packages, manufactured and/or delivered to your company (including your subsidiaries and affiliated company) directly or indirectly by our company (including our subsidiaries or affiliated companies) do not intentionally contain any of the substances listed in all applicable EU directives and regulations, including the following substances.

Exhibit A: The Harmful Material List

Material	Cd	Pb	Hg	Cr6+	PBB	PBDE	DEHP	BBP	DBP	DIBP
Limited	100	1000	1000	1000	1000	1000	1000	1000	1000	1000
Value	ppm	ppm	ppm	ppm	ppm	ppm	ppm	ppm	ppm	ppm
Above limited value is set up according to RoHS.										

- 2.Process for RoHS requirement : (only for RoHS inspection)
 - (1) Use the Sn/Ag/Cu soldering surface; the surface of Pb-free solder is rougher than we used before.
 - (2) Heat-resistance temp. :

Reflow: 250°C,30 seconds Max.;

Connector soldering wave or hand soldering: 320°C, 10 seconds max.

(3) Temp. curve of reflow, max. Temp. : 235±5°C;

Recommended customer's soldering temp. of connector: 280°C, 3 seconds.

DESIGN . MANUFACTURE . SUPPLY

Recommendable Storage

- 1. Place the panel or module in the temperature 25°C±5°C and the humidity below 65% RH
- 2. Do not place the module near organics solvents or corrosive gases.
- 3. Do not crush, shake, or jolt the module.