

# GRM21A5C2E270FW01D

“#” at the end indicates the package specification code.



## < List of part numbers with package codes >

GRM21A5C2E270FW01D      GRM21A5C2E270FW01J

## Applications

|                         |  |
|-------------------------|--|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use."  |
| Specific Applications   | Consumer equipment, Industrial Equipment, Mobile Electronics, Medical equipment [GHTE A/B/C] except for implant equipment, Automotive infotainment/comfort equipment<br>Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |

## References

| Packaging | Specifications         | Standard Packing Quantity |
|-----------|------------------------|---------------------------|
| D         | φ180mm Reel Paper Tape | 4000                      |
| J         | φ330mm Reel Paper Tape | 10000                     |

| Mass (typ.) |        |
|-------------|--------|
| 1 piece     | 12.0mg |

## Appearance & Shape



**Attention**  
1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.  
2. This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM21A5C2E270FW01D

“#” at the end indicates the package specification code.

## Specifications

|  |                |
|--|----------------|
| Length   | 2.0±0.2mm      |
| Width  | 1.25±0.2mm     |
| Thickness  | 1.0+0/-0.3mm   |
| Capacitance                                      | 27pF ±1%       |
| Distance between external terminals g            | 0.7mm min.     |
| External terminal size e                         | 0.3mm min.     |
| Operating Temperature Range                      | -55°C to 125°C |
| Rated Voltage                                    | 250Vdc         |
| Size code in inch(mm)                            | 0805 (2012M)   |
| TC   | 0±30ppm/°C     |
| Temperature characteristics (complied standard)  | C0G(EIA)       |
| Temperature range of temperature characteristics | 25°C to 125°C  |

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.