



## CJ1W-AD04U

Universal analog input unit, 4 x inputs 1 to 5 V, 0 to 5 V, 0 to 10 V, 0 to 20 mA, 4 to 20 mA, thermocouple (K, J, T, L, R, S, B), Pt100, Pt1000, JPt100, screw terminal

# Specifications

<b>I/O system</b>	CJ I/O Bus
<b>Expansion unit type</b>	Special I/O Unit
<b>Type of module</b>	Analog I/O
<b>Number of analog inputs</b>	4
<b>Temperature input type</b>	B, J, JPt100, K, L, Pt100, Pt1000, R, S, T
<b>Linear analog input type</b>	0 to 10 V, 0 to 20 mA, 0 to 5 V, 1 to 5 V, 4 to 20 mA
<b>Resolution of the analog inputs</b>	14 Bit
<b>Number of analog outputs</b>	0
<b>Linear analog output type</b>	None
<b>Conversion time</b>	12000 ms/unit
<b>I/O connection type</b>	Screw
<b>Number of I/O connectors</b>	1
<b>Detachable I/O connector</b>	✓
<b>Suitable for safety functions</b>	✗
<b>Product Height (unpacked)</b>	90 mm
<b>Product Width (unpacked)</b>	31 mm
<b>Product Depth (unpacked)</b>	89 mm
<b>Product Weight (unpacked)</b>	230 g

## CAD Library



### CJ-Series Analog I/O Units for NJ-Series (CJ1W-PDC15, -PH41U, -AD04U)

Operation Manual

EN PDF 2.03 MB



### CJ1 Universal Analog Input Units

Operation Manual

EN PDF 1020 KB



### CJ1W-AD/DA/MAD Analog I/O Unit

Datasheet

EN PDF 1.66 MB



### CJ1W-AD04U(-SL)

Instruction Sheet

EN PDF 119 KB



### CJ2-Series Programmable Controller

Datasheet

EN PDF 17.3 MB



### EAC Mark removal Discontinuation Notice

EN PDF 221 KB