


T356J685K050AT

T356, Tantalum, MnO2 Tantalum, Commercial Grade, 6.8 uF, 10%, 50 VDC, Radial, Solid Tantalum, Conformal, Dipped, 5.08mm



Click [here](#) for the 3D model.

Dimensions

D	8.4mm
H	14mm
S	5.08mm +/-0.38mm
LL	4.75mm +/-0.81mm
F	0.5mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	100

General Information

Series	T356
Dielectric	MnO2 Tantalum
Style	Radial
Description	Radial, Solid Tantalum, Conformal, Dipped
Features	Low Leakage, Reverse Voltage
RoHS	Yes
Termination	Tin
AEC-Q200	No
Notes	Longest Lead Is Positive.

Specifications

Capacitance	6.8 uF
Capacitance Tolerance	10%
Voltage DC	50 VDC (85C), 33 VDC (125C), 0.5 VDC (125C Reverse)
Temperature Range	-55/+125°C
Dissipation Factor	5%
Leakage Current	2.7 uA