



Pan-Ty® PLT.7M-M30 Cable Tie, Black, High Heat PA6.6, 3.1"L, 18lb, PK1000

PLT.7M-M30

Panduit PLT.7M-M30 Locking Cable Ties are designed to satisfy the needs of high temperature applications, while delivering consistent performance and reliability. Featuring a curved tip to allow for easy pick up from flat surfaces and faster initial threading. Miniature cross section, 3.1" (79mm) length. Made of Heat Stabilized Nylon 6.6, are black in color and come in packages of 1000.

Specifications

Product Type	Premium Cable Tie
Color	Black
Environment	Indoor
Material	Nylon 6.6
Material Properties	Heat-Stabilized
Resistance Properties	Heat-Resistant
Overall Length (In.)	3.1
Overall Length (mm)	79
Body Width (In.)	0.09
Body Width (mm)	2.3
Body Thickness (In.)	0.032
Body Thickness (mm)	0.8
Maximum Bundle Diameter (In.)	0.68
Maximum Bundle Diameter (mm)	17
Minimum Bundle Diameter (In.)	0.03
Minimum Bundle Diameter (mm)	0.8
Minimum Loop Tensile Strength (N)	80
Minimum Loop Tensile Strength (lb)	18
Maximum Operating Temperature (°C)	115
Maximum Operating Temperature (°F)	239
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Minimum Installation Temperature (°C)	-20
Minimum Installation Temperature (°F)	-4
Standards Met	UL Recognized (File #E56854), UL 62275 Compliant (Type 2, 21), RoHS Compliant
For Use With	GTS-E, GS2B-E, PTS, PPTS, STS2

Specifications (continued)

Part Features	One-piece locking wedge for consistent performance and reliability. Low thread force and high loop tensile strength.
---------------	--

Packaging Detail

UPC	07498352602
Std. Pkg. Qty.	1000
Std. Pkg. Volume (cf)	0.0359
Std. Ctn. Qty.	50000
Std. Ctn. Volume (cf)	1.7943