

Wirewound Resistors, Open Air, Current Sense, Low Value



FEATURES

- Open air design
- Low resistance values for all types of current sensing, voltage division and pulse applications including switching and linear supplies, instrumentation and power amplifiers
- All welded construction
- Solid metal nickel-chrome or copper-nickel alloy resistive element
- Solderable terminations
- Very low inductance
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



Pb-free


RoHS*
Available
HALOGEN
FREE
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	POWER RATING $P_{70^{\circ}\text{C}}$ W	RESISTANCE RANGE Ω	TOLERANCE $\pm \%$
SR3	3.0	0.0025 to 0.10	1, 2, 3, 5, 10
SR5	5.0	0.0025 to 0.05	1, 2, 3, 5, 10


TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	SR RESISTOR CHARACTERISTICS
Temperature Coefficient +25°C / -55°C; +25°C / +125°C	ppm/°C	$\pm 400 = 0.0025 \Omega$ to 0.0199Ω ; $\pm 300 = 0.02 \Omega$ to 0.049Ω ; $\pm 250 = 0.05 \Omega$ to 0.99Ω ; $\pm 200 = 0.1 \Omega$ and above
Operating Temperature Range	°C	-65 to +275
Maximum Continuous Current	A	$(P/R)^{1/2}$

GLOBAL PART NUMBER INFORMATION

Global Part Numbering example: SR55L000JE66

S	R	5	5	L	0	0	0	J	E	6	6			
GLOBAL MODEL		VALUE			TOLERANCE			PACKAGING			SPECIAL			
SR3 SR5		L = m Ω (below 0.01 Ω) R = decimal 5L000 = 0.005 Ω R0100 = 0.01 Ω			F = $\pm 1.0 \%$ G = $\pm 2.0 \%$ H = $\pm 3.0 \%$ J = $\pm 5.0 \%$ K = $\pm 10 \%$			E66 = lead (Pb)-free bulk			(dash number) (up to 3 digits) from 1 to 999 as applicable			

DIMENSIONS in inches [millimeters]


MODEL	DIMENSIONS in inches [millimeters]				
	A	B	C	E	F
SR3	$0.600 \pm 0.040/-0.020$ [15.24 ± 1.020/- 0.508]	1.0 maximum [25.4 maximum]	0.125 ± 0.030 [3.18 ± 0.762]	$0.065 \pm 0.010/-0.005$ [1.65 ± 0.254/- 0.127]	0.040 ± 0.002 [1.02 ± 0.051]
SR5	$0.800 \pm 0.040/-0.020$ [20.32 ± 1.020/- 0.508]				


MATERIAL SPECIFICATIONS

Element: nickel-chrome or copper-nickel alloy depending on resistance value

Terminals: tinned copper

Encapsulation: none

Marking: none

DERATING


PERFORMANCE		
TEST	CONDITIONS OF TEST	TEST LIMITS
Temperature Cycling	-55 °C to +125 °C, 5 cycles, 15 min at each extreme	$\pm (2.0 \% + 0.0005 \Omega) \Delta R$
Low Temperature Storage	-65 °C for 24 h	$\pm (0.5 \% + 0.0005 \Omega) \Delta R$
Mechanical Shock	100 g's for 11 ms, 5 pulses	$\pm (0.2 \% + 0.0005 \Omega) \Delta R$
Vibration	Frequency varied 10 Hz to 2000 Hz in 1 min, 3 directions, 12 h	$\pm (0.2 \% + 0.0005 \Omega) \Delta R$
Load Life	1000 h at rated power, +70 °C, 1.5 h "ON", 0.5 h "OFF"	$\pm (2.75 \% + 0.0005 \Omega) \Delta R$
Resistance to Solder Heat	+260 °C solder, 10 s to 12 s dwell	$\pm (0.2 \% + 0.0005 \Omega) \Delta R$
Short Time Overload	5x rated power for 5 s	$\pm (1.25 \% + 0.0005 \Omega) \Delta R$
Damp Heat	103B of MIL 202F and test condition "D", humidity chamber per 1300 h	$\pm (0.5 \% + 0.0005 \Omega) \Delta R$ no mechanical damage



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.