

SRV6KI

APC Easy UPS On-Line, 6kVA/6kW, Tower, 230V, Hard wire 3-wire(1P+N+E) outlet, Intelligent Card Slot, LCD



Overview

Presentation	High quality, Double-conversion On-line UPS designed for essential power protection needs even in the most unstable power conditions.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V
Product or component type	Uninterruptible power supply (UPS)
Input voltage	220 V 240 V
Output voltage	230 V
Output voltage	220 V 240 V
Rated power in W	6000 W
Rated power in VA	6000 VA
Output connector type	Hard wire 3-wire (1P + N + E) 1
Provided equipment	1 USB cable 1 RS-232 configuration cable 1 user manual
Range of product	Easy UPS On-Line

Batteries & Runtime

Battery type	Lead-acid battery
Battery voltage	192 V
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	4 H
Battery life	3...5 Year(S)
Battery charger power	235 W rated

General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No

Physical

Colour	Black (RAL 7010)
Height	68.5 Cm
Width	19 Cm
Depth	37.4 Cm
Net weight	54 Kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
USB compatible	Yes
Mounting position	Vertical

Input

Input voltage limits	110...300 V 60 % load 176...300 V full load
Number of input connectors	1 hard wire 3-wire (1P + N + E)
Network frequency	40...70 Hz auto sensing

Output

Maximum configurable power in VA	6000 VA
Maximum configurable power in W	6000 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Harmonic distortion	1 %
UPS type	Double conversion online
Wave type	Sine wave
Efficiency	94 % (full load)
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Bypass type	Internal bypass (automatic and manual)
Crest factor	3 : 1

Conformance

Product certifications	CE[RETURN]UKCA[RETURN]EAC[RETURN]TISI
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-15...60 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...15000 M
Acoustic level	55 dBA
Heat dissipation	1172 Btu/H
IP degree of protection	IP20

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous-tone alarm
Emergency power off	Yes
Free slots	1
Control panel	Multifunction LCD status and control console

Surge Protection and Filtering

Surge energy rate	600 J
-------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	91 Cm
Package 1 Width	29 Cm
Package 1 Length	49.5 Cm
Package 1 Weight	66 Kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Logistical informations

Country of origin	CN
-------------------	----

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **Commercialised**