

**RoHS
Compliant**

Description

This is a 1-part, acrylic-silicone blend conformal coating that cures to a durable, flexible and smooth finish. It is easy to apply and can be handled in only 8 minutes. It may be removed with appropriate strippers or soldered through for repair or rework.

This is designed for applications where both high service temperature and flexibility are required. It puts minimum stress on components during thermal cycling, making it ideal for applications that involve a wide temperature range. It provides strong protection against moisture, corrosion, fungus, dirt, dust, thermal shock, short circuits, high-voltage arcing, and static discharge.

Features and Benefits

- Certified UL 94 V-0 (File# E203094)
- Maximum service temperature of 200°C
- Fluoresces under UV-A light
- Suitable for use with selective coating equipment
- Excellent corrosion resistance

Storage and Handling

Store between -5°C and 40°C in a dry area.

Usage Parameters

Dry Time To Handle (1 coat)	: 8 min
(2 coats)	: 15 min
Minimum Recoat Time	: 3 min
Recommended Film Thickness	: 25–75µm
Theoretical Coverage @ 25 µm	: 70 000 cm ² /L

Brush

This can be applied by brush for rework or touch-ups. Thinning is not required for most brush applications. Desired coating thickness can be achieved in a single application. Applied coating can be cured immediately.

Cured Properties

Resistivity	: $1.2 \times 10^{15} \Omega\text{cm}$
Dielectric Strength	: 1 056 V/mil
Dielectric Withstand Voltage	: >1 500 V
Dielectric Constant @ 1 MHz	: 1.99
Dissipation Factor @ 1 MHz	: 0.012
Glass Transition Temperature (Tg)	: 29°C
CTE prior Tg	: 275 ppm/°C
Service Temperature Range	: -40°C to 200°C

Uncured Properties Without Colorants

Viscosity @ 25°C	: 10 cP
Density	: 0.9 g/mL
Percent Solids	: 28 %
Shelf Life	: 5 y
Calculated VOC	: 289 g/L

Cure Instructions

Allow to dry at room temperature for 48 hours, or after letting sit for 8 minutes, cure the coating in an oven for 20min @ 65°C.

Manual Spray Guns

Use a standard fluid nozzle gun with a minimum tip diameter of 0.8–1.0 mm. The settings listed below are recommendations; however, performance will vary with different brands:

Inlet	Air flow	Air cap
20–40 psi	10–15 SCFM	8–10 psi

1. Dilute 1-part coating to 1-part thinner (Thinner). Adjust ratio if required.
2. Stir the coating gently, but thoroughly.
3. Spray a test pattern to ensure good flow quality.
4. Tilt the board at 45° and spray a thin even coat from a distance of 20–25 cm (8–10 in). Use spray-and-release strokes with an even motion to avoid paint buildup in one spot. Start and end each stroke off the surface.
5. Wait 3 min between coats to avoid trapping solvent.
6. Rotate the board 90° and spray again to ensure good coverage.
7. Apply additional coats until desired thickness is achieved (go to step 3).
8. Let dry for 8 min at room temperature before applying heat cure.

Dip Coat

Use a Ford or Zahn cup to monitor the viscosity of the coating, as the solvent will evaporate over time.

1. Hang the PCB on a dipping arm.
2. Slowly lower the PCB into the tank and leave immersed in the coating for 2 min to allow penetration.
3. Slowly withdraw the PCB from the tank at a rate of approximately 6" per minute.
4. Let dry for 3 min before applying additional coats or 8 min before heat cure.

Selective Coating

For higher volume applications, coating can be applied via selective coating equipment. The settings listed below are recommendations and performance will vary with different brands.

Settings	PVA	Nordson Asymtek
Platform	PVA 650	SL 940E
Valve	FCM100	SC 280N
Dilution	None	None
Air Pressure	N/A	80 psi
Fluid Pressure	17 psi	23 psi
Dispense Height	10 mm	12.7 mm
Pass Width	8 mm	N/A
Coating Speed	400 mm/sec	381 mm/sec

Part Number Table

Description	Part Number
Conformal Coating, Silicone, 55mL	MP014781

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.