

**RoHS  
Compliant**




## Features

- Robust design with high degree of Accuracy and Compact size
- Frequency independent for AC applications
- Indicates operating time in hours and tenths with running indicators
- Totally sealed from Dust and Moisture
- Panel mountable with 7 Bezel options
- 6 Digit Non-Resetable with automatic recycle to zero
- Wide supply voltage range: 4 - 30V AC/DC, 10 - 80V DC & 90 - 264V AC
- Shock & Vibration Proof

## Specifications

Part Number	MP008420
<b>Parameters</b>	
Supply Voltage	90V AC to 264V AC
Frequency	50Hz to 60Hz
Over Voltage & Reverse Polarity Protection	NA
Power Consumption	0.5VA
Bezel	Square Mount
Register	6 Digit (3.6mm)
Read Out	99999.9
Least Count	1/10 h
Accuracy	± 0.02% over entire range
Vibration	10-80Hz with 20g max (SAE J1378)
Shock	55g @ 9-13ms (SAE J1378)
Weight (unpacked)	47g
Temperature	-40° C to +85° C
Humidity (Non Condensing)	95% (Rh)
Mounting	Panel
Termination	¼" [6.35mm] Spade Terminal
Degree of Protection	IP 66

## Diagram



Dimensions : Millimetres

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

**multicomp<sup>PRO</sup>**

## Features



- Suitable for Hour meter & Counter (Up / Down) application
- Wide Hour meter range from 1 sec to 9999999 hrs
- Wide counter range from 1 to 9999999 counts
- Prescaling facility for Counter
- Alarm facility for both Hour meter & Counter
- Relay & MOSFET Output with Over Load detection
- Retentive & Non-Retentive modes
- 7 Digit LCD with luxurious green backlight
- Compact size
- Suitable for panel mounting

## Specifications

<b>Part Number</b>		<b>MP008422</b>	
<b>Parameters</b>			
Supply Voltage		85 - 265V AC/DC	
Power Consumption (W)		2 VA / 1W	
Supply Frequency		50Hz to 60Hz	
<b>I/P Signal Characteristics</b>			
Signal Voltage Range		85 - 265 VAC & 100 - 265 VDC	
Signal Isolation		2kV	
<b>Output Characteristics</b>			
Output type		Relay: 1 C/O, Contact Rating: 5 A(Res.) @ 250V AC/30V DC Contact Material: Ag Alloy	
<b>Functional Characteristics</b>			
Display		7 digit LCD , 6.5 mm Height, 12 O' Clock, Transmissive	
Number of keys		2 (SET key & RST key)	
Reset function	Reset type	Auto Reset	
	Time (min.)	-	
Hour Meter Functions	Accuracy	± 2sec per Day	
	Ranges	Hrs : Min : Sec (999:59:59), Hrs : Min (99999:59), Hrs (9999999), Min (9999999), Sec (9999999)	
	Input Signal	For Hour counting detection, Signal has to be present for min. 3msec & signal has to be absent for min 20msec.	
Counter Functions	Accuracy	100%	
	Range	1 to 99999999.999	
	Decimal Point Position(max.)	3	
	Pre-scale	4 Digit	
	Input	Switching Freq.(max.)	10 Hz for AC and 40 Hz for DC
	Signal	Pulse Width min	50ms ON/50ms OFF for AC, 12.5ms ON/12.5ms OFF for DC

Environmental Characteristics	
Operating Temperature	-5°C to +55°C
Storage Temperature	-10°C to +60°C
Humidity	5 to 95% Rh (Without condensation)
Maximum Operating Altitude	2000 m
Pollution Degree	II
Degree of Protection	Front side: IP40; Terminals: IP20, Housing : IP30
Enclosure material	UL 94 V0 Plastic
Casing colour	Black
Other Characteristics	
Mounting	Flush mounting on panel cut-out
Panel Cut-out	22mm × 44.8mm
Weight (Un-packed)	52 gm
Operating position	Horizontal
Termination wire Sizes	Wire size : 22-14 AWG, 0.3-2.5 mm

## Views Of Different Bezels



Rectangular Bezel



Rectangular 2 holes Bezel



Round Bezel



Round 3 holes Bezel



Cup Mount Bezel



Stirrup Mount Bezel



**MP008423**



**MP008424**

## Features

- 6-digit LCD
- In-built nonvolatile memory (EEPROM) offering exceptional reliability
- Wide range of supply voltage
- Remote reset
- Available in 3 different Bezels
- Low Power Consumption

## Specifications

Part Number	MP008423	MP008424
<b>Parameters</b>		
Supply Voltage	12V DC to 48V DC	85V AC to 265V AC
Frequency	50/60 Hz	
Power Consumption (Max.)	0.4 W	0.8 VA
Counting frequency	10Hz	
Maximum Range	999999	
Display	Large 6-Digit display, easy to read	
Resolution	1 Count	
Reset	Electrical	
Memory Retention	100 Years	
Operating Temperature	-10°C to +50°C	
Storage Temperature	-20°C to +65°C	
Accuracy	± 1 Count	
Humidity (Non Condensing)	95% (Rh)	
Degree of Protection	IP54	
Enclosure	UL94-V0	
Terminals	1 & 2: Input Supply, 3: Count 4: Reset	
Panel cut outs	Round Bezel, 24 x 48 Bezel, Screw Mount Bezel	
Mounting	Flush/ Panel Mounting	
Weight (unpacked)	With Round Bezel - 35g, with 24 x 48 Bezel - 29 g, with Screw Mount Bezel - 31 g	



MP008425



MP008426

## Features

- 6-digit LCD
- In-built nonvolatile memory (EEPROM) offering exceptional reliability
- Wide range of supply voltage
- Remote reset
- Available in 3 different Bezels
- Low Power Consumption

## Specifications

Part Number	MP008425	MP008426
<b>Parameters</b>		
Supply Voltage	12V DC to 48V DC	85V AC to 265V AC
Frequency	50/60 Hz	
Power Consumption	0.4 W	0.8 VA
Range	99999.9 h	
Display	6-digit LCD 5mm Height	
Resolution	1/10 h	
Accuracy	± 0.02%	
Memory Retention	100 Years	
Operating Temperature	-10°C to +50°C	
Storage Temperature	-20°C to +65°C	
Humidity	95% (Rh)	
Degree of Protection	IP54 (for front side only)	
Enclosure	UL94-V0	
Terminals	1, 2: Input Supply, 3: Enable 4: Reset	
Panel cut outs	Round Bezel, 24 x 48 Bezel, Screw Mount Bezel	
Mounting	Flush / Panel Mounting	
Weight (unpacked)	IP 66 With Round Bezel- 35g, with 24 x 48 Bezel- 29 g, with Screw Mount Bezel- 31 g	

## Part Number Table

Description	Part Number
Digital Hour Meter, Square Mount Bezel, 90 - 264V AC	MP008420
Digital Hour Meter, Square Mount Bezel, 10 - 80V DC	MP008421
Digital Hour Meter & Pulse Counter with relay output	MP008422
Digital Hour Meter, 24x48 Bezel	MP008425
Digital Hour Meter, 24x48 Bezel	MP008426
Digital Pulse Counter, 24x48 Bezel	MP008423
Digital Pulse Counter, 24x48 Bezel	MP008424

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.