


T350A104K035AT7301

Aliases (T350A104K035ATTR)

T350, Tantalum, MnO₂ Tantalum, Commercial Grade, .1 uF, 10%, 35 VDC, Radial, Solid Tantalum, Conformal, Dipped, 2.54mm



Click [here](#) for the 3D model.

Dimensions

D	4.5mm
H	7.1mm
S	2.54mm +/-0.38mm
F	0.5mm +/-0.05mm

Packaging Specifications

Packaging	T&R, 305mm
Packaging Quantity	1500

General Information

Series	T350
Dielectric	MnO ₂ Tantalum
Style	Radial
Description	Radial, Solid Tantalum, Conformal, Dipped
Features	Low Leakage
RoHS	Yes
Termination	Tin
AEC-Q200	No
Notes	Longest Lead Is Positive.

Specifications

Capacitance	.1 uF
Capacitance Tolerance	10%
Voltage DC	35 VDC (85C), 23 VDC (125C), 0.35 VDC (125C Reverse)
Temperature Range	-55/+125°C
Dissipation Factor	3%
Leakage Current	0.5 uA