



Connectors > Connector Accessories > Connector Hardware



Hardware Accessory Function: **Mounting**
 Connector Hardware Accessory Type: **Bolster Assembly**
 Primary Product Material: **Stainless Steel**
 Operating Temperature (Max): **100 °C**
 Operating Temperature Range: **-40 – 100 °C**

Features

Product Type Features

Sealable	No
Hardware Accessory Function	Mounting
Connector Hardware Accessory Type	Bolster Assembly

Body Features

Insulator Material	Polycarbonate Film Plus Acrylic Adhesive Layer
Primary Product Material	Stainless Steel

Dimensions

Product Width	79 mm
Product Length	119 mm
Product Height	22.94 mm

Usage Conditions

Operating Temperature (Max)	100 °C
Operating Temperature Range	-40 – 100 °C

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Customers Also Bought



TE Part #6123001-1
0.8FH, P08H.5, 040, 30/Sn, TR, SC



TE Part #1-2324271-3
RIGHT SEGMENT LGA4189-4
SOCKETP4 FOR ODM



TE Part #1-2328461-1
280 POS., CONNECTOR ASSEMBLY,
SLIVER 2.0



TE Part #1-2397198-1
SOCKET 4710 FOR ODM



TE Part #2405569-1
LGA4710 BACKPLATE ASSY, SHORT
STUD



TE Part #2405570-1
LGA4710 E2A CARRIER ASSY



TE Part #1-2351053-3
LGA4677/LGA4710 SOCKET COVER



TE Part #2-2328461-1
280 POS., CONNECTOR ASSEMBLY,
SLIVER 2.0



TE Part #2274483-6
USB 3.0 RA RECEPTACLE



TE Part #2274483-7
USB 3.0 RA RECEPTACLE

Documents

Product Drawings

[LGA4710 TFLM ASSEMBLY W/O COVER](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_2405568-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2405568-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2405568-1_A.3d_stp.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.