



Click [here](#) for the 3D model.

Dimensions

D	20.2mm +/-0.5mm
L	35.7mm +/-1mm
LL	3.3mm +/-0.5mm
F	1mm +/-0.03mm

Packaging Specifications

Packaging	Tray
-----------	------

General Information

Series	PHH223
Dielectric	Hybrid Polymer
Style	Radial Crown
Description	Hybrid Radial Crown Capacitors
RoHS	Yes
Lead	Radial Crown
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	true
Typical Component Weight	20 g
Shelf Life	520 Weeks

Specifications

Capacitance	6800 uF
Capacitance Tolerance	20%
Voltage DC	25 VDC
Temperature Range	-40/+125°C
Rated Temperature	125°C
ESR	44 mOhms (100Hz 20C), 3.6 mOhms (100kHz - 40C to 125C)
Ripple Current	49.3 Amps (100kHz 90C), 46.3 Amps (100kHz 105C), 32.3 Amps (100kHz 125C)
Leakage Current	850 uA