

Color: ■ yellow

Similar to illustration

Technical data

Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	3,000 labels/reel; 2 lines
Printing device	Smart Printer (thermal transfer printer)

Physical data

Depth	0.06 mm
Marking surface	6 x 15 mm

Mechanical data

Mounting type	Sticking
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data

Color	yellow
Material	Polyester
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	Acrylic; permanent
Halogen-free	Yes
Weight	99.4 g
Fire load	0 MJ

Environmental requirements

Ambient temperature (storage)	+10 ... +21 °C
Ambient temperature (operation)	-40 ... +150 °C
Relative humidity	40 ... 50 %

Commercial data

eCl@ss 10.0	27-40-06-29
eCl@ss 9.0	27-40-06-29
ETIM 9.0	EC001288
ETIM 8.0	EC001288
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821632672
Customs tariff number	39199080888

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance


Compliance Search

Environmental Product
Compliance
210-805/000-002



Documentation

Operating Instructions

210-805 Information on handling print material	1 28.08.2020	pdf 1338.18 KB	
---	-----------------	-------------------	---

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marking device



Item No.: 258-5000

Thermal transfer printer; Smart Printer; for
complete control cabinet marking; 300
dpi; With marking material