

Product datasheet

Specifications



TeSys GF - impulse relay - 16 A - 2 NO - 24 V AC 50/60 Hz coil

Local distributor code:

380920509

GF1620B7

⚠ Discontinued on: 15 Jun 2023

EAN Code: 3389110707809

⚠ Discontinued

Main

Range	TeSys
Product name	TeSys GF
Product or component type	Impulse relay
Device short name	GF16
Utilisation category	AC-1
Poles description	2P
Pole contact composition	2 NO
[Ie] rated operational current	16 A AC-1
[Ue] rated operational voltage	250 V AC 50/60 Hz
Permissible short-time rating	320 A 40 °C 1 s 48 A 40 °C 30 s 96 A 40 °C 10 s
Operating position	+/- 90° to vertical plane
Control circuit type	AC at 50/60 Hz
[Uc] control circuit voltage	24 V AC 50/60 Hz
Mounting mode	Clip-on
Mounting support	35 mm symmetrical DIN rail

Complementary

[Ith] conventional free air thermal current	16 A (at 50 °C)
Average impedance	4 mOhm at 50 Hz - Ith 16 A
[Ui] rated insulation voltage	400 V conforming to IEC 60947-5-1 400 V conforming to VDE 0110
[Uimp] rated impulse withstand voltage	4 kV in enclosure
Connections - terminals	Control circuit: screw clamp terminals 1 cable(s) 1.5 mm ² solid without cable end Control circuit: screw clamp terminals 1 cable(s) 2.5 mm ² flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 2.5 mm ² flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 1.5 mm ² flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1.5 mm ² solid without cable end Control circuit: screw clamp terminals 2 cable(s) 2.5 mm ² flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 0.5...6 mm ² flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 0.5...6 mm ² flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 0.5...6 mm ² solid without cable end Power circuit: screw clamp terminals 2 cable(s) 0.5...4 mm ² flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 0.5...4 mm ² flexible without cable end Power circuit: screw clamp terminals 2 cable(s) 0.5...4 mm ² solid without cable end

Tightening torque	Control circuit: 0.8 N.m - on screw clamp terminals Power circuit: 0.8 N.m - on screw clamp terminals
Operating time	70 ms closing 70 ms opening
Maximum operating rate	900 cyc/h
Control circuit voltage limits	0.85...1.1 Uc 50 °C 50/60 Hz
Impulse duration	>= 70 ms
Average consumption	19 VA AC 50 Hz at at Uc at 20 °C
Power dissipation per pole	1 W
Mechanical durability	1 Mcycles
Electrical durability	100000 cycles AC-22 200000 cycles AC-21
9 mm pitches	2
Height	81 mm
Width	18 mm
Depth	64 mm
Net weight	0.11 kg
Quantity per set	Set of 12

Environment

Standards	IEC 60669-1 NF C 61-112 IEC 60669-2
IP degree of protection	IP40 conforming to VDE 0106 (in enclosure) IP20 conforming to VDE 0106
Protective treatment	TC
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...80 °C
Operating altitude	<= 2000 m without derating
Mechanical robustness	Vibrations contactor open: 4 Gn, 5...300 Hz Vibrations contactor closed: 4 Gn, 5...300 Hz

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	9.2 cm
Package 1 Length	23.0 cm
Package 1 Weight	119.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8.0 cm
Package 2 Width	9.2 cm
Package 2 Length	23.0 cm

Package 2 Weight	1.434 kg
Unit Type of Package 3	S02
Number of Units in Package 3	48
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	6.168 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

Rohs Exemption Information [Yes](#)

Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive [Compliant with Exemptions](#)

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile [End of Life Information](#)