

EMI-Ferrite Bead

Automotive



AB0203BED-KIT JIS 2012, 3216 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Impedance Ω (at 100MHz)	Tolerance (±%)	RDC(Ω) Max.	Rated Current (mA)	Quantity
ABPY00201209100Y00	2.0	1.2	0.9	2012/0805	10	25	0.01	6000	20
ABUP00201209220Y00	2.0	1.2	0.9	2012/0805	22	25	0.012	6000	20
ABPY00201209300Y00	2.0	1.2	0.9	2012/0805	30	25	0.015	4000	20
ABUP00201209300Y00	2.0	1.2	0.9	2012/0805	30	25	0.012	6000	20
ABUP00201209500Y00	2.0	1.2	0.9	2012/0805	50	25	0.015	6000	20
ABBK00201209600Y00	2.0	1.2	0.9	2012/0805	60	25	0.15	500	20
ABGK00201209600Y00	2.0	1.2	0.9	2012/0805	60	25	0.1	900	20
ABPY00201209600Y00	2.0	1.2	0.9	2012/0805	60	25	0.03	3000	20
ABUP00201209600Y00	2.0	1.2	0.9	2012/0805	60	25	0.018	6000	20
ABBK00201209800Y00	2.0	1.2	0.9	2012/0805	80	25	0.15	500	20
ABGK00201209800Y00	2.0	1.2	0.9	2012/0805	80	25	0.1	800	20
ABPY00201209800Y00	2.0	1.2	0.9	2012/0805	80	25	0.04	3000	20
ABUP00201209800Y00	2.0	1.2	0.9	2012/0805	80	25	0.02	6000	20
ABUP00201209101Y00	2.0	1.2	0.9	2012/0805	100	25	0.02	5000	20
ABBK00201209121Y00	2.0	1.2	0.9	2012/0805	120	25	0.25	300	20
ABGK00201209121Y00	2.0	1.2	0.9	2012/0805	120	25	0.15	800	20
ABPY00201209121Y00	2.0	1.2	0.9	2012/0805	120	25	0.04	3000	20
ABUP00201209121Y00	2.0	1.2	0.9	2012/0805	120	25	0.02	5000	20
ABBK00201209201Y00	2.0	1.2	0.9	2012/0805	200	25	0.3	300	20
ABPY00201209201Y00	2.0	1.2	0.9	2012/0805	200	25	0.05	2500	20
ABUP00201209201Y00	2.0	1.2	0.9	2012/0805	200	25	0.04	3000	20
ABBK00201209221Y00	2.0	1.2	0.9	2012/0805	220	25	0.3	300	20
ABGK00201209221Y00	2.0	1.2	0.9	2012/0805	220	25	0.18	750	20
ABPY00201209221Y00	2.0	1.2	0.9	2012/0805	220	25	0.08	2000	20
ABUP00201209221Y00	2.0	1.2	0.9	2012/0805	220	25	0.04	3000	20
ABBK00201209301Y00	2.0	1.2	0.9	2012/0805	300	25	0.3	300	20
ABGK00201209301Y00	2.0	1.2	0.9	2012/0805	300	25	0.18	700	20
ABPY00201209301Y00	2.0	1.2	0.9	2012/0805	300	25	0.08	2000	20
ABUP00201209301Y00	2.0	1.2	0.9	2012/0805	300	25	0.05	3000	20
ABUP00201209331Y00	2.0	1.2	0.9	2012/0805	330	25	0.05	3000	20
ABBK00201209471Y00	2.0	1.2	0.9	2012/0805	470	25	0.4	300	20
ABPY00201209471Y00	2.0	1.2	0.9	2012/0805	470	25	0.1	2000	20
ABBK00201209601Y00	2.0	1.2	0.9	2012/0805	600	25	0.4	300	20
ABGK00201209601Y00	2.0	1.2	0.9	2012/0805	600	25	0.25	500	20
ABPY00201209601Y00	2.0	1.2	0.9	2012/0805	600	25	0.1	2000	20
ABBK00201209102Y00	2.0	1.2	0.9	2012/0805	1000	25	0.5	200	20
ABGK00201209102Y00	2.0	1.2	0.9	2012/0805	1000	25	0.3	400	20
ABPY00201209102Y00	2.0	1.2	0.9	2012/0805	1000	25	0.12	1500	20
ABPY00321611300Y00	3.2	1.6	1.1	3216/1206	30	25	0.015	4000	20
ABUP00321611300Y00	3.2	1.6	1.1	3216/1206	30	25	0.012	6000	20
ABPY00321611500Y00	3.2	1.6	1.1	3216/1206	50	25	0.02	4000	20
ABPY00321611600Y00	3.2	1.6	1.1	3216/1206	60	25	0.02	4000	20
ABUP00321611600Y00	3.2	1.6	1.1	3216/1206	60	25	0.012	6000	20
ABPY00321611800Y00	3.2	1.6	1.1	3216/1206	80	25	0.025	3000	20
ABUP00321611800Y00	3.2	1.6	1.1	3216/1206	80	25	0.012	6000	20
ABPY00321611101Y00	3.2	1.6	1.1	3216/1206	100	25	0.03	3000	20
ABUP00321611101Y00	3.2	1.6	1.1	3216/1206	100	25	0.012	6000	20
ABBK00321611121Y00	3.2	1.6	1.1	3216/1206	120	25	0.15	500	20
ABPY00321611121Y00	3.2	1.6	1.1	3216/1206	120	25	0.03	3000	20
ABUP00321611121Y00	3.2	1.6	1.1	3216/1206	120	25	0.012	6000	20

EMI-Ferrite Bead

Automotive



AB0203BED-KIT JIS 2012, 3216 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Impedance Ω (at 100MHz)	Tolerance (±%)	RDC(Ω) Max.	Rated Current (mA)	Quantity
ABUP00321611151Y00	3.2	1.6	1.1	3216/1206	150	25	0.02	4500	20
ABBK00321611221Y00	3.2	1.6	1.1	3216/1206	220	25	0.2	400	20
ABPY00321611221Y00	3.2	1.6	1.1	3216/1206	220	25	0.05	2000	20
ABUP00321611221Y00	3.2	1.6	1.1	3216/1206	220	25	0.02	4500	20
ABBK00321611301Y00	3.2	1.6	1.1	3216/1206	300	25	0.2	400	20
ABPY00321611301Y00	3.2	1.6	1.1	3216/1206	300	25	0.06	2000	20
ABPY00321611391Y00	3.2	1.6	1.1	3216/1206	390	25	0.06	2000	20
ABPY00321611401Y00	3.2	1.6	1.1	3216/1206	400	25	0.1	2000	20
ABPY00321611471Y00	3.2	1.6	1.1	3216/1206	470	25	0.1	2000	20
ABPY00321611501Y00	3.2	1.6	1.1	3216/1206	500	25	0.1	2000	20
ABBK00321611601Y00	3.2	1.6	1.1	3216/1206	600	25	0.3	400	20
ABPY00321611601Y00	3.2	1.6	1.1	3216/1206	600	25	0.1	2000	20
ABPY00321611102Y00	3.2	1.6	1.1	3216/1206	1000	25	0.15	1200	20

EMI-Ferrite Bead


Automotive

YAGEO
GROUP
PULSE

AB0203BED-KIT JIS 2012, 3216 Size


Dimensions – Millimeters (Inches)

2012



Dimensions in mm	
TYPE	201209
A	2.00±0.20
B	1.25±0.20
C	0.90±0.20
D	0.50±0.30

3216



Dimensions in mm	
TYPE	321611
A	3.2±0.20
B	1.6±0.20
C	1.1±0.20
D	0.5±0.30